

# Product datasheet

Specifications



## Metal Outlet grille - cut-out 317x91mm ext dim 345x118mm IP20

Local distributor code:  
398242509

NSYCAG317X91M

**EAN Code: 3606480151781**

### Main

Range	ClimaSys
Product	ClimaSys CA
Product or component type	Metal louvre plate
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Mounting location	Sides of enclosure
Fixing mode	By screws
Device composition	1 fixing elements 1 metal louvre

### Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Cut-out dimensions	317 x 91 mm
Height	External: 345 mm
Width	External: 118 mm
IP degree of protection	IP20

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	12.500 cm
Package 1 Length	7.000 cm
Package 1 Weight	368.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	1.500 cm
Package 2 Width	12.500 cm
Package 2 Length	35.000 cm
Package 2 Weight	1.844 kg

## Logistical informations

---

Country of origin ES

## Contractual warranty

---

Warranty (in months) 18

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number

72d219a9-b35d-4262-a64d-01b587b0ccb7

REACH Regulation

[REACH Declaration](#)

## Use Again

### Repack and remanufacture

End of life manual availability

No need of specific recycling operations

Take-back

No