

HyFlex™

11-574

High-tactility cut-resistant glove



Cut



Light Duty

Boosts precision and productivity with second-skin comfort in an ANSI A4/ISO D-rated glove

- **Proven Productivity:** Users wearing HyFlex 11-574 safety gloves completed precision tasks 57% faster than using comparable gloves on the market*.
- **Second-Skin Design:** Engineered with AEROFIT™ Technology, an innovative, flexible foam nitrile coating delivering improved control and tactility – 94% of glove wearers reported improved fingertip control and tactile sensitivity^.
- **Premium Comfort:** 98% of professionals preferred HyFlex 11-574 for precision handling tasks and all-day wear^.
- **Advanced Cut Protection:** Features next generation INTERCEPT™ reinforced HPPE yarn for reliable ANSI/ISEA 105-2024 A4/ EN ISO D cut resistance when handling sharp or rough-edged objects.
- **Improved Compliance:** Reduced glove removal during shifts thanks to touchscreen compatibility and certified skin-friendliness.

* Comparison is based on Ansell lab tests under standardized conditions in December 2025 versus similar competitive gloves. Results may vary by application.

^Based on a survey of 52 glove wearers comparing Ansell gloves to competitive gloves available on the market (May 2025)



Industries

- Aerospace
- Machinery and Equipment
- Automotive

Applications

- Handling parts with sharp, rough edges
- Dry food handling & packaging
- Body Surface checking, marking and touching up
- Assembly of small parts
- Assembly & inspection of components

HyFlex™

11-574

High-tactility cut-resistant glove

Key Features

- ◊ **Productivity-enhancing design:** Enables 57% faster precision work.*
- ◊ **AEROFIT™ coating:** An innovative, flexible foam nitrile coating made up to 30% thinner** for exceptional tactility and control.
- ◊ **Breathable 21-gauge liner:** Delivers premium comfort in precision handling.

* Comparison is based on Ansell lab tests under standardized conditions in December 2025 versus similar competitive gloves. Results may vary by application.

** Versus standard Ansell glove with the same level of protection.

Technologies

 **AEROFIT™**
Precision Comfort Technology



DMF free

 **INTERCEPT™**
Cut Resistance Technology



Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3X31D



1408033

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex™ 11-574	Finishing: Palm Coated Coating Material: Foam Nitrile Cuff Style: Knitwrist	21	5, 6, 7, 8, 9, 10, 11, 12	229-279 mm / 9-11 inches	Black	• 12 pairs/paper band, 12 paper bands/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

