



Electronic time-delay switch 0.5 to 10 min adjustable max.: 400W

Model		
product brand name		DELTA
product designation		Electronic timer
design of the switching function		Off, 1-pole,
type of composition		basic element with complete enclosures
General technical data		
surface processing		other
material		Thermoplastic
operating voltage rated value		230 V
Protection class		
protection class IP		IP20
Dissipation		
power loss [W] for rated value of the current at AC in hot operating state per pole		400 W
Main circuit		
operational current rated value		1.7 A
Adjustable parameters		
adjustable time		
• initial value		0.5 min
• full-scale value		10 min
Appearance		
appearance		not applicable
color		white
Product details		
number of NC contacts		0
number of NO contacts		0
number of CO contacts		0
product feature		
• halogen-free		Yes
• transparent		No
Mechanical Design		
fastening method		flush mounting
net weight		35.8 g
material of the enclosure		other
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TG2400>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TG2400>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TG2400

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/26/2025 

