



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**  
Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

|                                         |                    |
|-----------------------------------------|--------------------|
| Insertion & Extraction Tool Type        | Contact Extraction |
| Insertion & Extraction Tool Application | Contact-to-Housing |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Out of Scope                                                                                                                  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1827855-1  
0.50 SERIES CONNECTOR  
RECEPTACLE CONTACT

Also in the Series | 0.50 Connector System

Automotive Connector Caps & Covers  
(20)

Automotive Headers(26)

Automotive Housings(52)

Automotive Terminals(14)

Connector Seals & Cavity Plugs(2)

PCB Headers & Receptacles(26)

Rectangular Power Connectors(1)

Wire-to-Board Headers & Receptacles  
(26)

Customers Also Bought


TE Part #1746872-1  
0.64III 12POS PLUG ASSY

TE Part #1612123-1  
SQUIB FERRITE

TE Part #353537-1  
040-3 UNSEALED CONT.TAB(S)

TE Part #2822344-1  
MINI MLC CAP HSG ASSY 7P






TE Part #1276565-1  
EXTRACTION TOOL FOR .025 REC



TE Part #1612121-4  
SQUIB 2POS PLUG HSG



TE Part #1612124-8  
1DIA SOCKET AU



TE Part #1827120-1  
SQUIB LOCKING BUTTON



TE Part #CAT-D9934-A75B  
Receptacle and Tab Housing: 5.08 mm Pitch, 250-600V

Documents

Product Drawings

EXTRACTION TOOL

Japanese

Product Specifications

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

Japanese

EXTRACTION TOOL FOR 0.50 SERIES REC. CONTACT

Japanese

Instruction Sheet (non U.S.)

Japanese