

# Eaton 135633

Catalog Number: 135633

Eaton Moeller® series E58 Diffuse reflective sensor, Sn=150mm, 4L, 10-30VDC, NPN, PNP, M18, insulated material, M12 13107RSQD07

### General specifications



#### Product Name

Eaton Moeller® series E58 Diffuse reflective sensor

#### Catalog Number

135633

#### EAN

4015081324262

#### Product Length/Depth

158.75 mm

#### Product Height

50.8 mm

#### Product Width

133.35 mm

#### Product Weight

0.32 kg

#### Certifications

CSA

CE

UL File No.: E117028

UL Category Control No.: NRKH, NRKH7

CSA Class No.: 3211-07

CSA File No.: 50513

CSA-C22.2 No. 14

IEC/EN 60947-5-2

UL

UL 508

## Product specifications

### Type

Optical sensors

### Features

Right-angled beam

### Electric connection type

Connector M12

### Enclosure material

Plastic

### Enclosure type

Cylinder, screw-thread

### Operating mode

Switching principle: Adjustable bright/dark switching

### Explosion safety category for dust

None

### Explosion safety category for gas

None

### Functions

Short-circuit protection

Protection against polarity reversal

Detection of transparent objects

Reflected-light beam

### Voltage type

DC

### Wire size

22

### Connection type

4-wire

Plug-in connection M12 x 1

### Cable sheath material

Polyvinyl chloride (PVC)

### Light type

Infrared light

### Degree of protection

NEMA 6

IP67

### Interface type

## Resources

### Catalogs

[Product Range Catalog Sensors](#) – products, basic information, applications

### Declarations of conformity

[DA-DC-00004652.pdf](#)

[DA-DC-00004657.pdf](#)

### Drawings

[eaton-proximity-switches-dimensions-002.eps](#)

[eaton-proximity-switches-3d-drawing-006.eps](#)

### Installation instructions

[IL05305002Z](#)

### mCAD model

[DA-CD-90\\_28267\\_112](#)

[DA-CS-90\\_28267\\_112](#)

Other

#### LED indicator

Status indication of Switching state: Red LED

#### Switch function type

Other

#### Load current

Max. 100 mA (I<sub>e</sub>, PNP)

Max. 250 mA (I<sub>e</sub>, NPN, 120 > 50°C)

#### Laser protection class

None

#### Operation agent-safety class

Safety class 2

#### Shock resistance

100 g, Mechanical, Shock duration 3 ms

#### Optical surface material

Plastic

#### Output current (mA) - max

250 mA

#### Output current at protected output - max

0 mA

#### Rated control supply voltage (U<sub>s</sub>) at AC, 50 Hz - max

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 50 Hz - min

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 60 Hz - max

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 60 Hz - min

0 V

#### Rated control supply voltage (U<sub>s</sub>) at DC - max

30 V

#### Rated control supply voltage (U<sub>s</sub>) at DC - min

10 V

#### Rated switching distance (S<sub>n</sub>)

150 mm

#### Reflector distance - min

0 mm

#### Sensor height

0 mm

Sensor length

66 mm

Switching distance - max

150 mm

Switching voltage of OSSD at state high

0 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

500 Hz

Sensing mode

Light-/dark switching

Switching output type

NPN

Sensor material

Insulated material

Wavelength of the sensor

0 nm

Width sensor

0 mm

Product category

Comet Series

Response time

1 ms

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-40 °C

Diameter sensor

18 mm

Light dot size

0 mm<sup>2</sup>

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operating distance - max

0 mm

Operating distance - min

0 mm

Operational current (Ib) in the switched state at 24 V DC

30 A

Adjustment type

Manual adjustment



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia