




Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Insert for Contacts**

Contact Type: **Socket**

Pole Configuration: **22**

Number of Positions: **22**

Wire Size: **16 AWG**

Features

Product Type Features

Rectangular Connector Insert Type	Insert for Contacts
-----------------------------------	---------------------

Configuration Features

Number of Positions	22
---------------------	----

Body Features

Seal Type	Grommet Seal, Interfacial Seal
-----------	--------------------------------

Contact Features

Contact Type	Socket
Pole Configuration	22

Mechanical Attachment

Polarization Code	B
-------------------	---

Dimensions

Wire Size	16 AWG
-----------	--------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #7-2151639-7
[OCEAN_2.0_SPARE_PART_KIT-055F075O0700](#)




TE Part #87175-4
[15 LOCKING CLIP HSG SR .100CL](#)




TE Part #592104-2
[TJ SEALING PLUG,SZ 16](#)




TE Part #592104-1
[PLUG,SEALING,SZ 20](#)




TE Part #1738166-1
[INSERT ASY,PIN,E,30-P,KEY A](#)



TE Part #1738151-1
[Insert Asy,Pin,Arr 22,Environ,Key B](#)



TE Part #1738169-1
[INSERT ASY,SOCKET,E,30P,KEY A](#)



TE Part #920672-000
[ST63-4-55-22-9](#)



Documents

Product Drawings

Insert Asy,Skt,Arr 22,Environ,Key B

English

CAD Files

Customer View Model

ENG_CVM_CVM_1738154-1_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1738154-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1738154-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ARINC 600 Next Generation Receptacle Connector

English