

Product datasheet

Specifications



SELECTOR SWITCH OPERATOR 30MM T-K

9001K53J35LGFG

EAN Code: 3389118042889

Main

Range of product	Harmony 9001K
Product or component type	Head for illuminated selector switch
Device short name	9001K
Type of operator	To centre spring return
Operator profile	Green long handle

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Net weight	0.245 kg
Shape of signaling unit head	Octagonal
Operator position information	3 positions
Contacts type and composition	Without contact block
Mechanical durability	500000 cycles
Light block supply	Direct
Light source	LED
Bulb base	BA 9s
Light block colour	Green
[Us] rated supply voltage	24 V AC/DC
Product compatibility	9001KA1, mounted side 1 or 2
Device presentation	Basic element
Cap/operator or lens colour	Green
[Us] rated supply voltage	24...28 V
Light source colour	Green
Operator profile	Long handle
Type of operator	Spring return
Size	30 mm
Return	Both sides to centre
Light source	LED
Cam profile	3

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP65 IP66
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4
Standards	JIS C 4520 IEC 60947-5-4 JIS C 852 IEC 60947-5-1 UL 508 CSA C22.2 No 14 IEC 60947-1
Product certifications	UL 508 NEMA
Vibration resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.572 cm
Package 1 Width	5.334 cm
Package 1 Length	9.144 cm
Package 1 Weight	249.476 g

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty (in months)	18
----------------------	----


Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.



[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration

Use Again

 Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins