

MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/gb/products/1329819>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic converter with LC duplex connection (1310 nm) for 100Base-TX to multimode fiber optics, DIN rail mountable.

Product description

The MC 1000-MM LC media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber optics port with an LC connector.

Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 100 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring

Commercial data

Item number	1329819
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNC314
Product key	DNC314
GTIN	4063151625719
Weight per piece (including packing)	191.4 g
Weight per piece (excluding packing)	124 g
Customs tariff number	85176200
Country of origin	CA

MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/gb/products/1329819>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Media converter
MTTF	86.4 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	756.3 Years ()
	370.3 Years (Telcordia standard, temperature 25 °C, operating cycle 100 % (7 days a week, 24 hours a day))

Electrical properties

Supply

Supply voltage range	12 V DC ... 48 V DC
Nominal supply voltage	24 V DC
Typical current consumption	20 mA (24 V DC)
Max. current consumption	170 mA

Connection data

Supply

Connection method	Push-in spring connection
Conductor cross section, flexible	0.20 mm² ... 2.50 mm²
Conductor cross section, rigid	0.20 mm² ... 2.50 mm²
Conductor cross section, flexible [AWG]	24 ... 12
Conductor cross section AWG	24 ... 12
Stripping length	10.00 mm

Interfaces

Signal	Ethernet
--------	----------

Data: optical FO

Transmit capacity, minimum	-20 dBm (62.5/125 µm, multimode fiberglass)
	-23.5 dBm (50/125 µm, multimode fiberglass)
Transmit capacity, maximum	-14 dBm
Transmission length incl. 3 dB system reserve	2 km
Connection method	LC duplex
Wavelength	1310 nm

MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/gb/products/1329819>

Minimum receiver sensitivity	-31 dBm
Maximum receiver sensitivity	-8 dBm
Transmission medium	Multi-mode fiberglass

Data: Ethernet interface, 100Base-Tx in acc. with IEEE 802.3u

Transmission speed	10/100 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LNK/ACT, SPD, US
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

Dimensions

Width	22.5 mm
Height	123 mm
Depth	90 mm

Material specifications

Housing material	Polyamide fiber reinforced
------------------	----------------------------

Cable/line

FO cable

Fiber types	50/125 µm
	62.5/125 µm
	Fiberglass

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 5g, 150 Hz, Criterion 3
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 30g, 11 ms half-sine shock pulse

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (in acc. with UL)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Shock	300 m/s ² , 11 ms (IEC 60068-2)

Approvals

MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/gb/products/1329819>

Conformity/Approvals

Conformance	CE-compliant
UL, USA / Canada	UL 61010-1, UL 61010-2-201

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Comments	Criterion B
----------	-------------

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Comments	Criterion A
----------	-------------

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Comments	Criterion A
----------	-------------

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge current load (surge)

Comments	Criterion B
----------	-------------

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Comments	Criterion A
----------	-------------

Emitted interference

Standards/regulations	EN 55032
-----------------------	----------

Mounting

Mounting type	DIN rail: 35 mm
Mounting position	On horizontal DIN rail NS 35 in acc. with EN 60715

MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/gb/products/1329819>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1329819>



cULus Listed

Approval ID: E238705

MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/gb/products/1329819>

Classifications

ECLASS

ECLASS-13.0	19170411
-------------	----------

ETIM

ETIM 9.0	EC001467
----------	----------

UNSPSC

UNSPSC 21.0	43223323
-------------	----------

MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/gb/products/1329819>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk