



EN ISO 20345:2011



SCOUT

ORTISEI BOA®

30437-00L

S3 *CI HRO HI WR SRC

Size: 36-50

Weight: 780 gr.

Fit: 11

Working Environment:

Building, Wood-metal carpentry,
Farming and Gardening,
Multipurpose



FEATURES

UPPER

MicroFiber Suede 1,8-2,0 mm
No ladder H.T. Fabric
MicroFiber TOP 1,8-2,0 mm
Reflex insert

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Qrs01

TOE CAP

Alu SXT 2.0 Toe cap

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE

PU-RUBBER VIBRAM-FIRE&ICE

PU foam insole, light and comfortable. Modular overtow to protect uppers. VIBRAM rubber tread with Fire & ICE mix for high performance in all temperatures. Self-cleaning design with special SRC grip.

Boa® lace length

M4 - 120cm

TECHNOLOGIES

Removable Insole



Anatomical breathable insole. Resistant fabric with recycled open-cell foam that absorbs shocks and reduces fatigue. Eliminates sweat with its high ability to evaporate it. Continuous comfort for months and months of use



Protection elements



Toecap "Alu Sxt 2.0" with differentiated thicknesses, resistant to 200J. Non metal perforation resistant Insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamic HC control
technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.




Electrical features



Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other



FIT TO GO FURTHER™

A patented closing system with a multi coated stainless steel cable. The BOA® Fit System delivers micro-adjustable precision fit, engineered to perform in the toughest conditions.



SRC (SRA+SRB)



SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.53
	HEEL (CONTACT ANGLE °) ≥0.28	0.49
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.23
	HEEL (CONTACT ANGLE °) ≥0.13	0.18

EN ISO 20344:2011