
Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26KAAW21MPXS_36
COUPLING HALF: Coupler
CONNECTION SIZE: G 1/2
FUNCTION: Single Shut-Off
BODY MATERIAL: Brass
CONNECTION TYPE: Male BSPP

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:
- General Industrial
- Industrial manufacturing equipment

Features/Benefits:
- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

CONNECTION TYPE	BSPP
SLEEVE MATERIAL	Brass
DIVISION	Low Pressure Connectors Europe Division
INDUSTRY	Transportation
MAXIMUM OPERATING PRESSURE	507 psi
PRODUCT TYPE	Pneumatic Quick Couplings
VALVE INCLUDED	Yes
PLATING TYPE	Without Surface Treatment
INDUSTRY	General Industrial
LENGTH	44 mm
APPLICATION	Trucks & Trailers
CONNECTION TYPE	Male
OPERATION TYPE	Sleeve
INDUSTRY	Healthcare & Life Sciences
COMPATIBLE FITTING	Series 26 Plug
HEX SIZE	24 mm
TECHNOLOGY	Pneumatics
BODY MATERIAL	Brass
FLOW RATE	1070 L/min (air)
MAXIMUM OPERATING PRESSURE	35 bar
APPLICATION	Mobile & Defence
REGION OF ORIGIN	Germany
DIAMETER	7.2 mm (nominal)
BRAND	Parker
MAXIMUM OPERATING TEMPERATURE	100 °C
APPLICATION	Air & Gas Compressor

OUTSIDE DIAMETER	25 mm
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
BRAND	Rectus
MINIMUM OPERATING TEMPERATURE	-4 °F
APPLICATION	Industrial Machinery
DIVISION	Low Pressure Connectors Europe Division
QUANTITY PER BOX	10
WEIGHT	0.0913 kg
CONNECTION SIZE	G 1/2
MINIMUM OPERATING TEMPERATURE	-20 °C
APPLICATION	Safety & Rescue
VALVE TYPE	Standard Valve
PRODUCT STYLE	Quick-Connect
COUPLING HALF	Coupler
PRODUCT SERIES	Series 26
INTERCHANGE TYPE	European Profile
MAXIMUM OPERATING TEMPERATURE	212 °F
APPLICATION	Food & Beverages
FUNCTION	Single Shut-Off
SEAL MATERIAL	NBR