



- ▶ **Extended lever angle mount limit switch bracket**
- ▶ **All stainless steel construction**
- ▶ **Industry standard right-angle mounting**
- ▶ **Waterproof rated to IP68**

The E1264-508 is a great example of a robust limit switch with an all-stainless extended lever actuator. Completely made of high grade stainless steel, it is truly waterproof.

This switch has been designed to meet the operational and environmental demands of heavy-duty industrial applications.

CPI has achieved endurance qualifications over 5 million cycles with this basic limit switch design.

Typical Applications

- ▶ **Back-up Alarm Switch**
- ▶ **Cab Closed Interlock Switch**
- ▶ **Cab Down Sensor**
- ▶ **Compartment Door Light Switch**
- ▶ **Dishwasher Door Closed**
- ▶ **Door Interlock**
- ▶ **Door Switch**
- ▶ **Dump body Detect Switch**
- ▶ **Hopper Down Detect**
- ▶ **Interlock Switches**
- ▶ **Nozzle Position Sensing**
- ▶ **Outrigger Position Sensing**
- ▶ **Park Brake Switch**
- ▶ **Seat Position Switch**
- ▶ **Valve Position Sensing**

Specifications	
Electrical Rating	28 VDC / 120VAC 5A resistive, 3A inductive
Electrical Configuration	SPDT
Operating Temperature	-40 to 221°F / -40 to 105°C
Cover Material	Santoprene (thermoplastic) / bracket: 304 stainless steel
Endurance	100,000 cycles
Leads	18 AWG GXL insulated wire, 24" / 609.6 mm length

E1264-508 EXTENDED LEVER ANGLE MOUNT



Dimensions

