

Driver Drill LXT®, DDF492

18V, 141 Nm, 0 – 2 100 min⁻¹

Model DDF492 is a drill driver powered by an 18V LXT Li-Ion battery.

This improved model has a powerful maximum fastening torque of 141Nm. Features and benefits: Redesigned speed change mechanism to avoid gear disengagement. Controller protection has been revised to enhance the protection for electronic components during variable speed control by the trigger



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	0 - 550 / 0 - 2100 min ⁻¹
Max. fastening torque Hard/Soft	130 / 65 Nm
Max Torque	141 Nm
Torque setting	21
Max. Drilling Diameter in Wood	76 mm
Max. Drilling Diameter in Steel	13 mm
Drill Chuck Capacity	1,5 - 13 mm
Drilling Capacity Wood (Auger Bit)	50 mm
Drilling Capacity Wood (Self-feed bit)	76 mm
Vibration Level, Drilling into metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Drilling into metal	1,5 m/s ²
Sound Power Level (L _{WA})	88 dB(A)
Sound Pressure Level (L _{pA})	80 dB(A)

User benefits

- Highly efficient and compact machine for professional use
- Keyless chuck for easy bit installation and removal
- LED light illuminates the work site
- Electronic overload protection protects the user and the device
- Battery protection system automatically shuts off power when the battery level is low
- Compact and lightweight for reduced operator fatigue
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

■ Optional AC

821550-0
Makpac case (2)



837916-4
MakPac (2) Inlay



■ Other

User manual

Parts drawing