

ETP 15

Electronic torsion test device

0,5 - 3150 Nm / 0,4 - 2323 lbf·ft

Code	ETIM
2795663	EC011814
EAN	UNSPSC
4002805932957	27-11-27-20
Country of origin	eCl@ss
Germany	21-04-32-90
Customs tariff number	
90318080	



Article description

- For testing, and verifying clockwise and anti-clockwise torque wrenches
- 5 models in the range 0,5 - 3150 Nm
- 5 models in the range from 0,5 to 3.150 N·m
- Electronic torque tester integrated with measurement electronics
- Robust housing from aluminium cast (except ETP 3150) with separate or detachable operating display
- Serial interface RS232 for PC
- Traceable to national standards
- No. ETP 15 with integrated overload protection and tool for manual resetting after unintended overload
- Torque reading precision +/- 1 %, +/- 1 digit from reading figure
- Factory certificate based on VDI 2646
- Optional certificate as per DAkkS-DKD-R 3-8
- A large LC graphic display
- Wide measuring range in Nm, can be switched to cNm, lbf·ft or lbf·in (model dependant)
- Free evaluation PC software included
- Scope of delivery: Operating display, display holder incl. cable, software incl. connection cable for PC
- Adapter cable RS232 to USB optionally available (Code 1957880)•

Article information

Contents (Qty of pieces)	1	Torque (min.) [lbf·ft]	0,4 lbf·ft
Net weight [kg]	4,8 kg	Torque (max.) [lbf·ft]	11 lbf·ft
Total length [mm]	120 mm	Torque range (min./max.) [N·m]	0,5 Nm - 15 Nm
Total width [mm]	93 mm	Torque range (min./max.) [lbf·ft]	0,4 lbf·ft - 11 lbf·ft
Total height [mm]	80 mm	Resolution	0,001
Drive connector square female (metric)	6,3 mm	Measurement accuracy	± 1% Toleranz vom Ablesewert, ± 1 Digit
Drive connector square female [inch]	1/4"	Interface	RS-232
Torque (min.) [N·m]	0,5 Nm	Overload protection	yes
Torque (max.) [N·m]	15 Nm	Graphic display	yes