


DOC NO	ISSUE	REVISION	PRODUCT REF.	DATE	QUALITY PLAN
QF/RD/05	01	00	FAR0101	24.09.14	
<b>TECHNICAL SPECIFICATIONS</b>				<b>SIGNATURE</b>	
				<b>PRESIDENT (TECHNICAL)</b>	

## FULL BODY HARNESS (FAR0101)



### DESIGN

- One dorsal attachment D-ring for fall arrest.
- Adjustable leg straps.
- Adjustable chest straps.
- Sit Strap.
- Made up of elastic webbing for more comfort & impact resistant.

### WEBBING

- Material : Polyester.
- Width : 44±1mm.
- Breaking strength : 23 kN

### STITCHING THREAD

- Material : High-tenacity polyester.

### METAL COMPONENTS

- Material : Aluminium.
- Plating : Black anodized.
- Finish : Matt.

### VITAL TEST COMPLIANCE

- Static Strength : 15 kN or 1,530 kgf for 3 Minutes at each attachment element.
- Dynamic strength : Free fall from 4 meters height donned to a test dummy weighing 100 kg at each attachment element.


### WEIGHT

- : 1006 gm ±10 gm



DOC NO	ISSUE	REVISION	PRODUCT REF.	DATE	QUALITY PLAN
QF/RD/05	01	00	FAR0208	10.10.14	
<b>TECHNICAL SPECIFICATIONS</b>				<b>SIGNATURE</b>	
				<b>PRESIDENT (TECHNICAL)</b>	

## WORK POSITIONING LANYARD (FAR0208)



### DESIGN

- Adjustable length upto 2 meters maximum.
- Adjustment by use of ring type adjuster.
- Karabiners [116F(C)] provide at both end for attachment.

### WEBBING

- 33 MM Polyester Webbing.
- Breaking Strength greater than 30 kN.

### METAL COMPONENTS

- Material : Forged alloy steel ring type adjuster.
- Plating : Zinc plated.
- Finish : Deburred & Polished.

### VITAL TEST COMPLIANCE

- Static Strength : 15 kN for 3 Minutes.
- Dynamic strength : Free fall from 1 meter height with a test mass of 100 kg.

### WEIGHT

- 2.0 Meter : 587 gm  $\pm$ 10 gm.