

TeSys K contactor - 4P (2 NO + 2 NC) - AC-1 <= 440 V 20 A - 220...230 V AC coil

Local distributor code: 386125764 LC1K09008M7

EAN Code: 3389110488876

Main

Range	TeSys
Product or component type	Contactor
Device application	Control
Contactor application	Resistive load

Complementary

Complementary		
Utilisation category	AC-1	
Poles description	4P	
power pole contact composition	2 NO + 2 NC	
[Ue] rated operational voltage	Power circuit: <= 690 V AC <= 400 Hz Signalling circuit: <= 690 V AC <= 400 Hz	
[le] rated operational current	20 A (at <60 °C) at <= 690 V AC AC-1 for power circuit	
Control circuit type	AC at 50/60 Hz	
[Uc] control circuit voltage	220230 V AC 50/60 Hz	
[Uimp] rated impulse withstand voltage	8 kV	
Overvoltage category	III	
[Ith] conventional free air thermal current	20 A (at 60 °C) for power circuit 10 A (at 50 °C) for signalling circuit	
Irms rated making capacity	110 A AC for power circuit conforming to IEC 60947	
Rated breaking capacity	110 A at 220230 V conforming to IEC 60947 110 A at 380400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947	
[lcw] rated short-time withstand current	90 A 50 °C - 1 s for power circuit 85 A 50 °C - 5 s for power circuit 80 A 50 °C - 10 s for power circuit 60 A 50 °C - 30 s for power circuit 45 A 50 °C - 1 min for power circuit 40 A 50 °C - 3 min for power circuit 20 A 50 °C ->= 15 min for power circuit	
Associated fuse rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit	
Average impedance	3 mOhm - Ith 20 A 50 Hz for power circuit	
[Ui] rated insulation voltage	Power circuit: 600 V conforming to UL 508 Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V conforming to CSA C22.2 No 14	
Inrush power in VA	30 VA (at 20 °C)	

Hold-in power consumption in VA 4.5 VA (at 20 °C)		
Heat dissipation	1.3 W	
Control circuit voltage limits	Operational: 0.81.15 Uc (at <50 °C)	
	Drop-out: >= 0.20 Uc (at <50 °C)	
Connections - terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid	
	Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end	
	Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end	
	Screw clamp terminals 2 cable(s) 1.54 mm²solid	
	Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end	
	Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end	
Maximum operating rate	3600 cyc/h	
Signalling circuit frequency	<= 400 Hz	
Mounting support	Plate	
	Rail	
Tightening torque	0.81.3 N.m - on screw clamp terminals Philips No 2	
	0.81.3 N.m - on screw clamp terminals flat Ø 6 mm	
	0.81.3 N.m - on screw clamp terminals pozidriv No 2	
Operating time	1020 ms coil de-energisation and NO opening	
· · · · · · · · · · · · · · · · · · ·	1020 ms coil energisation and NO closing	
	1525 ms coil de-energisation and NC closing	
	515 ms coil energisation and NC opening	
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1	
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO	
	13849-1	
Mechanical durability	10 Mcycles	
Electrical durability	0.16 Mcycles 20 A AC-1 at Ue <= 690 V	
Mechanical robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27	
	Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27	
	Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27	
	Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27	
	Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-2	
	Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27	
	Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6	
	Vibrations contactor opened: 2 Gn, 5300 Hz conforming to IEC 60068-2-6	
Height	58 mm	
Width	45 mm	

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 IEC 60335-1:Clause 30.2 IEC 60335-2-40:Annex JJ
	UL 60335-2-40:Annex JJ
Product certifications	CB Scheme CCC UL CSA EAC CE UKCA
IP degree of protection	IP2X conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient air temperature for storage	-5080 °C

Operating altitude	2000 m without derating
Flame retardance V1 conforming to UL 94	
	Requirement 2 conforming to NF F 16-101
	Requirement 2 conforming to NF F 16-102

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	6.200 cm
Package 1 Length	4.800 cm
Package 1 Weight	177.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.265 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	91
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Offer Marketing Illustration

Product benefits / Features

TeSys K

Contactors



Flexibility

Designed with control voltages, low consumption, minimal noise levels, robust power connections, and a range of auxiliaries, and application-specific variants to meet diverse needs.



Safety

It provide ultimate protection with IP20 fingersafe terminals, built-in NO/NC auxiliary contacts, and IEC-certified mirror and mechanically linked contacts for safety applications.



Compact size

Up to 50% less volume is captured in your panels. One of he smallest contactors offerings in the market

Offer Marketing Illustration

Product benefits / Features

TeSys K

Technical Benefits



Up to 4 more by add-on blocks

Up to 16 A for motor control (AC3/ AC3E) and 20A for resistive load control (AC1)

Available as single contactors, star-delta, and reversing combos, with a wealth of options and accessories

Control Options:

- AC: 24 to 660/690 V, standard or low-noise versions
- DC: 12 to 250V, standard or low consumption (1.8 W) versions

Thermal protection relays

It Features specific versions for railway (TeSys \$207) and electrodomestic (TeSys \$335) applications



LC1K09008M7

Technical Illustration

Assembly's dimensions

