



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 16

Terminal Block Connector Type: Plug

Connector System: Wire-to-Board

Centerline (Pitch): 5.08 mm [.2 in]

Number of Rows: 1

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	16
Number of Rows	1
Wire Entry Angle	180°
Wire Entry Location	Side

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------



Product Orientation	Right Angle
---------------------	-------------

Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3
Connector Mounting Type	Board Mount

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Wire Size	30 – 12 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Marking Color	White
---------------	-------

Packaging Features

Packaging Method	Box
Packaging Quantity	50

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JUNE 2022 (224)
SVHC > Threshold:
Pb (2% in Component)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-282825-6
TERMI-BLOK HEADER, ASSY90 16P.5




TE Part # 1-796639-6
16POS 5.08MM CE R/A HDR, TRM BK



TE Part # 1-796637-6
16POS 5.08MM CE VRT HDR, TRM BK



TE Part # 1-796638-6
16POS 5.08MM CE R/A HDR, TRM BK



TE Part # 1-282815-6
TERMI-BLOK HEADER, ASSY90 16P.



TE Part # 1-796636-6
16POS 5.08MM CE VRT HDR, TRM BK

Customers Also Bought



TE Part #8-6609107-9
[PS0SXDSXB=C1306](#)

TE Part #9-2176370-4
[RQ 0603 4K02 0.1% 10PPM 5K RL](#)

TE Part #1SNA115486R0300
[MA2.5/5](#)

TE Part #2-36932-2
[TERMINAL,SOLIS R 4/0 1/4](#)

TE Part #640310-3
[UMNL SOK 12-10 PTPPHBZ](#)

TE Part #1-2176088-3
[RP 1J 0.166W 1K0 0.1% 25PPM 1K RL](#)

TE Part #42100-1
[FF 250 REC 18-14AWG BR](#)

TE Part #DT3P-BT
[BOOT, 3P, REC, ST, GRY](#)

TE Part #322451
[TERMINAL,SOLIS SPD 12-10 6](#)

TE Part #322996
[TERMINAL,SOLIS SPD 16-14 6](#)

Documents

Product Drawings

16 POS 5.08MM R/A PLUG,TRM BLK

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-796635-6_J.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-796635-6_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-796635-6_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English