



product details

QTP5 2X14-35/220-240 UNV1

Product description: QTP5 2X14-35/220-240 UNV1
 EAN/ Product: 4008321061539
 Quantity: Unpacked (UNV) contains 1 Piece (PCE)

Applications	
Dimmable	NO
Type of protection	IP20
Lamp start	preheat start within 1 s

General Description	
Design / version	ECG standard
Standards	acc. to EN 55015, CISPR 15 acc. to EN 61547 / IEC 61547 acc. to EN 61000-3-2 / IEC 61000-3-2 acc. to EN 61347-2-3 / IEC 61347-2-3
Energy Label - EEI	A2
Sstl-Number	4030206

Technical - Electrical Data	
Operating frequency	40 ... 50 kHz
Mains frequency	50-60 Hz
TH full width at half maximum	200 µs
Power factor c	0.98
Nominal voltage	220-240 V
DC voltage	154...276 V ¹⁾
IP inrush current	40 A
Max. no. of ECGs on circuit breaker 10A	11
Max. no. of ECGs on circuit breaker 16A	19
Dielectric strength	300 V - permanent / 320 V - 48 h / 350 V - 2h

Technical - Geometries	
Mounting hole spacing, length	415 mm
Width	30 mm
Height	21 mm
Length	423 mm

Technical - Temperatures	
Max. casing temp. in case of fault	110 °C
Max. operating temp. at the Tc point	75 °C
Ambient temperature range	-20 ... +50 °C
Storage temperature	-40 ... 85 °C
Relative humidity	5 ... 85 %; max. 56 d/y at 85 %

Packaging units				
EAN	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4008321061539	Unpacked contains 1 Piece	34,000 mm x 22,000 mm x 425,000 mm	302,500 g (0,000 g)	0,318 Cubic dec.
4008321061546	Shipping carton box contains 20 Piece	170,000 mm x 96,000 mm x 435,000 mm	6.184,000 g (0,000 g)	7,099 Cubic dec.



product details

QTP5 2X14-35/220-240 UNV1

system overview											
operation of ecg with	Length in mm	Number of lighting outlet	Length in mm	Width in mm	Height in mm	System power consumption in W (ECG)	System power consumption in W (CCG)	System power consumption in W (LLB)	Luminous flux with ECG in lumen	Luminous flux in lumen (CCG)	Power factor
HE 14	549 mm										
HE 21	849 mm										
HE 28	1149 mm										
HE 35	1449 mm										

¹⁾ lamp start only with more than 198 V_{DC}