

HOLTITE

TE Internal #: 4-1437514-4  
3.45 mm [.136 in] Socket Length, 1.61 mm [.064 in] PCB Hole, Open Bottom, .081 – .162 mm² Wire, 28 – 25 AWG, Cable-to-Board, Signal, Pin Sockets

[View on TE.com >](#)



Connectors > Socket Connectors > Pin Sockets



Socket Length: 3.45 mm [.136 in]  
PCB Hole Diameter: 1.61 mm [.064 in]  
Socket Sleeve Style: Open Bottom  
Wire Size: 28 – 25 AWG

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Open Bottom
Connector System	Cable-to-Board
Sealable	No

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Sleeve Plating Material	Tin
Sleeve Material	Copper

Contact Features

Contact Spring Plating Material	Tin
Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	.76 µm
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Insertion Method	Hand/Semi-Automatic/Automatic
Termination Method to Wire & Cable	Solder



Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm [.03 – .05 in]
Socket Length	3.45 mm [.136 in]
PCB Hole Diameter	1.61 mm [.064 in]
Wire Size	28 – 25 AWG
Mating Pin Diameter Range	.51 – .76 mm [.02 – .03 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Solder Process Feature	None
Circuit Application	Signal

Packaging Features

Packaging Method	Reel
Packaging Quantity	2000

Other

Spring Material	Beryllium Copper
-----------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Pb (.6% in Component) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-1437514-5  
399-HT-113="SEATING TOOL TIP,P

TE Part # 5-1437514-7  
399-HT-114=AUTOMATIC SEATING T

Customers Also Bought

TE Part #114017-ZZ  
SEALING PLUG, SIZE 12/16, WHT

TE Part #CAT-D48-ST273  
DEUTSCH Solid Contacts

TE Part #DT04-2P  
REC, 2P, GRY, N

TE Part #DT06-2S  
PLG, 2P, GRY, N

TE Part #CAT-D487-W416  
Wedgelocks: DEUTSCH DT

TE Part #CAT-AM71-CH8172  
AMP SUPERSEAL 1.5MM,  
CONNECTOR HOUSING

TE Part #281934-2  
SINGLE WIRE SEAL

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG\_CVM\_CVM\_4-1437514-4\_99.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437514-4\\_99.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437514-4\\_99.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English