

## SAFETY DATA SHEET 569-240 PENETRATING/EASING FLUID

### SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

#### 1.1. Product identifier

Product name 569-240 PENETRATING/EASING FLUID  
Product No. 000162069263

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Releasing agent.

#### 1.3. Details of the supplier of the safety data sheet

Supplier R S Components Limited  
Birchington Road  
Corby  
Northants  
NN17 9RS  
+44(0)1536 402888 (8am-8pm)  
+44(0)1536 401588  
technical.help@rs-components.com

#### 1.4. Emergency telephone number

### SECTION 2: HAZARDS IDENTIFICATION

#### 2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Flam. Aerosol 1 - H222
Human health	EUH066;STOT SE 3 - H336
Environment	Not classified.

Classification (1999/45/EEC)

F+;R12. R66, R67.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

#### 2.2. Label elements

Label In Accordance With (EC) No. 1272/2008



Signal Word Danger

Hazard Statements

H222	Extremely flammable aerosol.
H336	May cause drowsiness or dizziness.

Precautionary Statements

P102	Keep out of reach of children.
P210	Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P271	Use only outdoors or in a well-ventilated area.
P261	Avoid breathing vapour/spray.
P280	Wear protective gloves.
P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+313	If eye irritation persists: Get medical advice/attention.
P501	Dispose of contents/container in accordance with local regulations.

Supplementary Precautionary Statements

P211	Do not spray on an open flame or other ignition source.
P251	Pressurized container: Do not pierce or burn, even after use.

**569-240 PENETRATING/EASING FLUID**

P264	Wash contaminated skin thoroughly after handling.
P304+340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P312	Call a POISON CENTER or doctor/physician if you feel unwell.
P403+233	Store in a well-ventilated place. Keep container tightly closed.
P410+412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.
Supplemental label information	
EUH066	Repeated exposure may cause skin dryness or cracking.
H229:	Pressurised container: May burst if heated.

**2.3. Other hazards****SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS****3.2. Mixtures**

BUTANE		5-10%
CAS-No.: 106-97-8	EC No.: 203-448-7	
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12	
ISOBUTANE		1-5%
CAS-No.: 75-28-5	EC No.: 200-857-2	
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12	
MINERAL OIL (REFINED)		1-5%
CAS-No.: 64742-52-5	EC No.: 265-155-0	
Classification (EC 1272/2008) Not classified.	Classification (67/548/EEC) Not classified.	
NAPHTHA (PETROLEUM), HYDROTREATED HEAVY		30-60%
CAS-No.: 64742-48-9	EC No.: 919-857-5	Registration Number: 01-2119463258-33-xxxx
Classification (EC 1272/2008) Flam. Liq. 3 - H226 EUH066 STOT SE 3 - H336 Asp. Tox. 1 - H304	Classification (67/548/EEC) Xn;R65. R10,R66,R67.	
PROPANE		10-30%
CAS-No.: 74-98-6	EC No.: 200-827-9	
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

**569-240 PENETRATING/EASING FLUID****SECTION 4: FIRST AID MEASURES****4.1. Description of first aid measures**

## General information

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

## Inhalation

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

## Ingestion

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

## Skin contact

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

## Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

**4.2. Most important symptoms and effects, both acute and delayed****4.3. Indication of any immediate medical attention and special treatment needed****SECTION 5: FIREFIGHTING MEASURES****5.1. Extinguishing media**

## Extinguishing media

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

**5.2. Special hazards arising from the substance or mixture**

## Unusual Fire &amp; Explosion Hazards

Aerosol cans may explode in a fire.

**5.3. Advice for firefighters**

## Special Fire Fighting Procedures

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

**SECTION 6: ACCIDENTAL RELEASE MEASURES****6.1. Personal precautions, protective equipment and emergency procedures****6.2. Environmental precautions****6.3. Methods and material for containment and cleaning up**

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

**6.4. Reference to other sections****SECTION 7: HANDLING AND STORAGE****7.1. Precautions for safe handling**

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

**7.2. Conditions for safe storage, including any incompatibilities**

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

**7.3. Specific end use(s)****SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION****8.1. Control parameters**

## 569-240 PENETRATING/EASING FLUID

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
BUTANE	WEL	600 ppm	1450 mg/m <sup>3</sup>	750 ppm	1810 mg/m <sup>3</sup>	
ISOBUTANE	WEL	800 ppm		800 ppm		
MINERAL OIL (REFINED)			5 mg/m <sup>3</sup>		10 mg/m <sup>3</sup>	
NAPHTHA (PETROLEUM), HYDROTREATED HEAVY			1000 mg/m <sup>3</sup>			
PROPANE		Asphyxiating	Asphyxiating.	Asphyxiating	Asphyxiating.	

WEL = Workplace Exposure Limit.

Ingredient Comments

OES = Occupational Exposure Standard. MEL = Maximum Exposure Limit.

## 8.2. Exposure controls

Protective equipment



Engineering measures

Provide adequate general and local exhaust ventilation.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. Use chemical cartridge protection with appropriate cartridge.

Hand protection

Use protective gloves.

Eye protection

Wear approved chemical safety goggles where eye exposure is reasonably probable.

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

Appearance	Aerosol.
Colour	Typical
Odour	Characteristic.
Flammability Limit - Lower(%)	3.0
Flammability Limit - Upper(%)	18.6

### 9.2. Other information

## SECTION 10: STABILITY AND REACTIVITY

### 10.1. Reactivity

### 10.2. Chemical stability

Stable under normal temperature conditions.

### 10.3. Possibility of hazardous reactions

### 10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

## 569-240 PENETRATING/EASING FLUID

**10.5. Incompatible materials****10.6. Hazardous decomposition products**

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

---

**SECTION 11: TOXICOLOGICAL INFORMATION**


---

**11.1. Information on toxicological effects****Inhalation**

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system.

**Ingestion**

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

**Skin contact**

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema.

**Eye contact**

Irritating to eyes.

**Route of entry**

Inhalation. Skin and/or eye contact.

---

**SECTION 12: ECOLOGICAL INFORMATION**


---

**Ecotoxicity**

Dangerous for the environment if discharged into watercourses.

**12.1. Toxicity****12.2. Persistence and degradability****12.3. Bioaccumulative potential****12.4. Mobility in soil****12.5. Results of PBT and vPvB assessment****12.6. Other adverse effects**


---

**SECTION 13: DISPOSAL CONSIDERATIONS**


---

**13.1. Waste treatment methods**

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

---

**SECTION 14: TRANSPORT INFORMATION**


---

**14.1. UN number**

UN No. (ADR/RID/ADN)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950

**14.2. UN proper shipping name**

Proper Shipping Name                      AEROSOLS

**14.3. Transport hazard class(es)**

**569-240 PENETRATING/EASING FLUID**

ADR/RID/ADN Class	2
ADR/RID/ADN Class	Class 2: Gases
ADR Label No.	2.1
IMDG Class	2.1
ICAO Class/Division	2.1
Transport Labels	

**14.4. Packing group**

ADR/RID/ADN Packing group	Not Applicable
IMDG Packing group	Not Applicable
ICAO Packing group	Not Applicable

**14.5. Environmental hazards**

Environmentally Hazardous Substance/Marine Pollutant  
No.

**14.6. Special precautions for user**

EMS	2-13
-----	------

**14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code****SECTION 15: REGULATORY INFORMATION****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Uk Regulatory References

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

Statutory Instruments

The Control of Substances Hazardous to Health Regulations 2002.

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

Guidance Notes

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

**15.2. Chemical Safety Assessment****SECTION 16: OTHER INFORMATION**

Revision Date	05/10/2015
Revision	5
Supersedes date	16/02/2015

**569-240 PENETRATING/EASING FLUID**

## Risk Phrases In Full

R12	Extremely flammable.
R10	Flammable.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

## Hazard Statements In Full

H222	Extremely flammable aerosol.
H220	Extremely flammable gas.
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H336	May cause drowsiness or dizziness.
EUH066	Repeated exposure may cause skin dryness or cracking.