

M18 FMTIW2F12-0X

M18 FUEL™ 1/2" MID-TORQUE IMPACT WRENCH WITH FRICTION RING

- Most versatile cordless impact wrench in the MILWAUKEE® impressive arsenal with an industry-leading performance at 881 Nm of nut-busting torque and 745 Nm of fastening torque
- Incredibly compact design for this performance level, with only 152 mm overall length ideal for applications in tight spaces
- 4-Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility
- Bolt removal control delivers full torque output, then decreases RPMs once the bolt is loosened to prevent fastener drops
- Auto shut-off control applies no more than 47 Nm of torque for hand-tight fastening applications to prevent over-tightening
- Tri-LEDs deliver high definition lighting to increase workspace visibility
- 1/2" square friction ring
- Reversible belt hook
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™

Impact rate (ipm)	0-900 / 0-2,100 / 0-3,100
No load speed (rpm)	0-1200/ 0-1950/ 0-2575/ 0-1325
Nut-busting torque (Nm)	881
Weight with battery pack (EPTA) (kg)	2.3 (M18 B5)
Kit included	No batteries supplied, No charger supplied, HD Box
Article Number	4933478449

