


Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26KEAW17MPN

COUPLING HALF: Coupler

CONNECTION SIZE: G 3/8

FUNCTION: Self-Venting

BODY MATERIAL: Brass

CONNECTION TYPE: Male BSPP

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:

- General Industrial
- Industrial manufacturing equipment

Features/Benefits:

- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

WEIGHT	0.096 kg
CONNECTION SIZE	G 3/8
APPLICATION	Air & Gas Compressor
INDUSTRY	Transportation
LENGTH	55 mm
COMPATIBLE FITTING	Series 25 Plug
INTERCHANGE TYPE	European Profile
MINIMUM OPERATING TEMPERATURE	-20 °C
MAXIMUM OPERATING PRESSURE	12 bar
PRODUCT SERIES	Series 26
MAXIMUM OPERATING TEMPERATURE	60 °C
APPLICATION	Trucks & Trailers
INDUSTRY	Electronics
MAXIMUM OPERATING TEMPERATURE	140 °F
MAXIMUM OPERATING PRESSURE	174 psi
FLOW RATE	830 L/min (air)
BRAND	Rectus
APPLICATION	Energy Management
INDUSTRY	General Industrial
MINIMUM OPERATING TEMPERATURE	-4 °F
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
DIAMETER	7.4 mm (nominal)
BRAND	Parker

APPLICATION	Mobile & Defence
CONNECTION TYPE	BSPP
VALVE TYPE	Standard Valve
PLATING TYPE	Nickel-Plated
OUTSIDE DIAMETER	31 mm
TECHNOLOGY	Pneumatics
SLEEVE MATERIAL	Brass
VALVE INCLUDED	Yes
FUNCTION	Self-Venting
DIVISION	Low Pressure Connectors Europe Division
QUANTITY PER BOX	5
DIVISION	Low Pressure Connectors Europe Division
PRODUCT TYPE	Pneumatic Quick Couplings
PRODUCT STYLE	Quick-Connect
COUPLING HALF	Coupler
HEX SIZE	22 mm
BODY MATERIAL	Brass
SEAL MATERIAL	NBR
APPLICATION	Electronics
OPERATION TYPE	Sleeve
CONNECTION TYPE	Male
REGION OF ORIGIN	Germany