

640051-1


✓ ACTIVE

TE Internal #: 640051-1

Closed Ring Tongue Terminal, 18 – 14 AWG, #8 / M4 Stud, 4.4 mm [.173 in] Stud Diameter, Open Barrel, Straight, Unplated Plating, Uninsulated

[View on TE.com >](#)

Terminals & Splices > Ring Terminals

Ring Terminal Product Type: **Closed Ring Tongue Terminal**Wire Size: **1624 – 4106 CMA**Stud Size: **#8, M4**

Features

Product Type Features

Shape Description	Anti-Rotational/Grounding
Terminal Features	Sheared
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	.553 g
----------------	--------

Contact Features

Contact Base Material	Stainless Steel
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Unplated

Contact Underplating Material

None

Mechanical Attachment

Wire Insulation Support

With

Dimensions

	.105 in
Wire Size	1624 – 4106 CMA
Stud Diameter	4.4 mm [.173 in]
Tongue Thickness	.61 mm [.024 in]
Product Length	19.56 mm [.77 in]
Barrel Inside Diameter	1.6 mm, 3.17 mm [.063 in] [.125 in]
Compatible Insulation Diameter (Max)	3.68 mm [.145 in]
Compatible Insulation Diameter Range	2.67 – 3.68 mm [.105 – .145 in]

Usage Conditions

Insulation Option

Uninsulated

Operating Temperature Range

-40 – 110 °C [-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material

Copper

Industry Standards

Government Qualified Terminal

No

Packaging Features

Packaging Quantity

6000

Packaging Method

Strip/Reel

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150911-1
OCEAN_2.0_Applicator-E-130F180F-
SEM



TE Part # 2150911-2
OCEAN_2.0_Applicator-E-130F180F-
SEA



TE Part # 350509-1
RING 22-16 AWG BR



TE Part # 2150008-2
OCEAN_2.0_Applicator-E-130F180F-
REA



TE Part # 7-2150911-7
OCEAN_2.0_SPARE_PART_KIT-
130F180F



TE Part # 2150008-1
OCEAN_2.0_Applicator-E-130F180F-
REM



TE Part # 7-2150008-7
OCEAN_2.0_SPARE_PART_KIT-
130F180F

Customers Also Bought



TE Part #803485-SF
FN2200-250-99



TE Part #2-36153-2
PIDG R 22-16 COMM 22-18 MIL 10



TE Part #42281-2
FF 250 REC 18-14AWG TPBR



TE Part #61177-2
250 FASTON FLAG REC 18-12 AWG
TPBR



TE Part #62001-2
SPLICE AMVAR 3000-7000 020TPBR



TE Part #177908-4
POWER DBL LOCK CAP HSG P/M 4P



TE Part #641775-1
04P UMNL STR/REL & INSRT NATL



TE Part #9-1393117-9
KUP-14A55-120-KU



TE Part #1903120-1
DYNAMIC D1000 TAB CONT TIN (M)
REEL



TE Part #1-2350416-0
DYNAMIC 1100D TAB HSG 40P P/M
GF33

Documents

Product Drawings

RING TONGUE .164 18-14 AWG SST

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_640051-1_W.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_640051-1_W.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_640051-1_W.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English