

Product datasheet

Specifications



ClimaSys forced vent. IP54, 38m3/h, 48V DC, with outlet grille and filter G2

Local distributor code:
388829385

NSYCVF38M48DPF

⚠ Discontinued on: 9 Feb 2023

⚠ Discontinued

EAN Code: 3606480151194

Main

Range	ClimaSys
product name	ClimaSys CV
Product or component type	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter: 44 m3/h
[Us] rated supply voltage	36...56 V
Input voltage	48 V DC

Complementary

Absorbed power	3.6 W
[In] rated current	0.07 A
Noise level < at	40...41 dB
Bearing type	Ball
Height	External: 137 mm
Width	External: 117 mm
Depth	External : 49 mm
Cut-out dimensions	92 x 92 mm
Net weight	0.23 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	29 Pa flow rate 0 m³/h
Connections - terminals	Cable
IP degree of protection	IP54
Device composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Condition of use	Outside temperature must be 5 °C lower than inside temperature Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software Filter must be cleaned and replaced regularly
------------------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	12.500 cm
Package 1 Length	14.700 cm
Package 1 Weight	280.000 g

Logistical informations

Country of origin	FR
-------------------	----


Contractual warranty

Warranty	18 months
----------	-----------


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

<div>Environmental footprint</div>	
Environmental Disclosure	Product Environmental Profile

Use Better

<div>Materials and Substances</div>	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	61d9d3f3-5a49-48f8-8056-1a5ad0ad4c76
REACH Regulation	REACH Declaration

Use Again

<div>Repack and remanufacture</div>	
Circularity Profile	End of Life Information
Take-back	No