



PRODUCT-DETAILS

OT315E04YP

OT315E04YP BY-PASS SWITCH



概要信息	
产品型号	OT315E04YP
产品ID	1SCA123583R1001
欧洲商品编号(EAN)	6417019543673
目录说明	OT315E04YP BY-PASS SWITCH
详细描述	Including a black plastic IP65 I-0-II pistol type handle and a handle extension for enabling smooth manual operation, shaft and bolt set for the cable connection. The handle extension is snap-on mounted on the standard handle for manual operation. The handle extension shall be removed when padlocking the standard handle. Handle padlockable in the 0-position, door interlock in the I- and II-positions and when padlocked.

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS信息	1SCC011020D0201
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Popular Downloads	
数据手册，技术资料	1SCC303003C0201
说明书和手册	1SCC301080M0003

环境条件	
防护等级	Front IP20
污染等级	3

订货信息	
最小起订量	1 piece
海关关税号	85365080
原产地	Finland (FI)

尺寸	
产品净宽	284 mm
	11.18 in
产品净高	185 mm
	7.28 in
产品净深	306 mm
	12.05 in
产品净重	13.6 kg
	29.98 lb

包装信息	
1级包装单元	box 1 box
1级包装宽度	265 mm
	10.43 in
1级包装长度	375 mm
	14.76 in
1级包装高度	330 mm
	12.99 in
1级包装 总重	14.02 kg
	30.91 lb
1级包装 EAN	6417019543673

技术参数	
额定发热电流（自由空气）(I _{th})	Θ = 40 °C 315 A
额定发热电流 (I _{the})	Fully Enclosed 315 A
防护等级	Front IP20
两相之间距离	Standard
第四个极位	Right Side
第四个极点类型	Switched - Simultaneous Function
Handle Color	Black
手柄类型	Handle and shaft included
安装类型	Base mounting
极数	4P

操作模式	Front operated
污染等级	3
导线端子位置	Top In - Bottom Out, Bottom In - Top Out
功率损耗	at Rated Operating Conditions per Pole 6.5 W
额定冲击耐受电压 (U _{imp})	12 kV
额定绝缘电压 (U _i)	1000 V
额定工作电流 AC-21A (I _e)	(380 ... 415 V) 315 A (500 V) 315 A (690 V) 315 A
额定工作电流 AC-22A (I _e)	(380 ... 415 V) 315 A (500 V) 315 A (690 V) 315 A
额定工作电流 AC-23A (I _e)	(380 ... 415 V) 315 A (500 V) 315 A (690 V) 315 A
额定工作功率 AC-23A (P _e)	(380 ... 415 V) 160 kW (500 V) 220 kW (690 V) 315 kW
额定工作电压	Main Circuit 1000 V
额定不间断电流 (I _{cw})	for 1 s 15 kiloampere rms
开关操作机构	Mechanism at the End of the Switch 04 (Left Side)
端子类型	Screw Terminals
拧紧力矩	acc. IEC 60947-1 30 ... 44 N·m
转换类型	Open

UL/CSA适用的技术参数

拧紧力矩	acc. IEC 60947-1 30 ... 44 N·m
------	--------------------------------

认证及声明（文件编码）

符合性声明 - CE	1SCC301195D2703
------------	-----------------

分类

对象分类代码	Q
ETIM 8	EC000216 - Switch disconnector
ETIM 9	EC000216 - Switch disconnector (low voltage)
e级	V11.1 : 27371403
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

分类

低压产品及系统 → 开关类产品 → 转换开关 → Manual Bypass Switches

