JHM15 Series

DC-DC Converter



15 Watts

- International Medical Approvals
- 4000 VAC Reinforced Insulation
- Medical Approval, IEC60601-1, 3rd Edition
- 2 µA Patient Leakage Current
- Compact 1 x 1.6" Footprint
- EN55011 Level A With No External Components
- 3 Year Warranty



Dimensions:

JHM15:

1.60 x 1.00 x 0.40" (40.60 x 25.40 x 10.20 mm)

Models & Ratings

Input Voltage	Output Voltage	Output Current	Input	Current	Maximum	Efficiency (4)	Model Number
input voitage		Output Current	No Load ⁽¹⁾	Full Load ⁽²⁾	Capacitive Load ⁽³⁾	Efficiency ⁽⁴⁾	
9-18 V	5.0 V	3000 mA	9.2 mA	1930 mA	3000 µF	87%	JHM1512S05
	12.0 V	1250 mA	6.5 mA	1938 mA	1330 µF	86%	JHM1512S12
	15.0 V	1000 mA	8.0 mA	1944 mA	1000 µF	86%	JHM1512S15
	±5.0 V	±1500 mA	6.6 mA	1955 mA	±1470 μF	84%	JHM1512D05
	±12.0 V	±625 mA	11.2 mA	1911 mA	±660 µF	87%	JHM1512D12
	±15.0 V	±500 mA	11.0 mA	1879 mA	±550 μF	88%	JHM1512D15
18-36 V	5.0 V	3000 mA	5.6 mA	972 mA	3000 µF	86%	JHM1524S05
	12.0 V	1250 mA	6.1 mA	968 mA	1830 µF	85%	JHM1524S12
	15.0 V	1000 mA	6.4 mA	966 mA	1000 µF	87%	JHM1524S15
	±5.0 V	±1500 mA	5.4 mA	981 mA	±1470 µF	83%	JHM1524D05
	±12.0 V	±625 mA	7.3 mA	954 mA	±660 µF	87%	JHM1524D12
	±15.0 V	±500 mA	8.5 mA	943 mA	±550 μF	87%	JHM1524D15


Notes

- 1. Input current measured at nominal input voltage.
- 2. Input current measured at lowest input voltage.

3. Maximum capacitive load is per output.

4. Typical values.

Mechanical Details



Pin Connections							
Pin	Single	Dual					
1	+Vin	+Vin					
2	-Vin	-Vin					
3	+Vout	+Vout					
4	-Vout	Common					
5	Trim	-Vout					
6	No Pin	No Pin					

Notes

- 1. All dimensions are in inches (mm)
- 2. Weight: 0.04 lbs (20 g) approx.
- 3. Pin diameter: 0.02 ±0.002 (0.5 ±0.05)
- 4. Pin pitch tolerance: ±0.01 (±0.25) 5. Case tolerance: ±0.02 (±0.5)

JHM15 Series



Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage Range	9		18	VDC	12 V nominal
	18		36	VDC	24 V nominal
Input Current					See Models and Ratings table
Inrush Current		20 A at 36 V		at 36 V	
Input Filter	Pi type	Pitype			
Patient Leakage Current			2	μA	
Undervoltage Lockout	On at >8.8 V. Of	ff <8.3 V		12 V models	
Ondervoltage Lockout	On at >17.5 V. O	off <17.0 V			24 V models
Input Surge			25	VDC	12 V models for 3 s
input Surge			50	VDC	24 V models for 3 s

Output Characteristic Minimum Typical Maximum Units Notes & Conditions Output Voltage 5 15 V See Models and Ratings table Output Voltage Trim ±10 % Via external resistors, see Application Notes ±1 % on V1 Initial Set Accuracy ±2 % on V2 of dual output models Minimum Load 0 А No minimum load required Start Up Delay 5 ms Start Up Rise Time 2 ms Line Regulation ±0.3 % ±2 % 0 - 10% load Load Regulation 10 - 100% load ±1 % On dual output models with one output set to 50% load and ±4 % **Cross Regulation** the other varied from 10% to 100% load (D05 20% to 100%) Recovery to within 1% in <500 µs for a 50% load change 4 Transient Response % deviation at 0.25 Å/µs rate Ripple & Noise 1 % pk-pk 20 MHz bandwidth Short Circuit Protection Trip & Restart (hiccup mode), auto recovery 120 200 % **Overload Protection** Trip & Restart (hiccup mode) 115 Overvoltage Protection 140 % Non latching, auto recovery 0.03 %/°C Temperature Coefficient

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		86		%	See Models and Ratings table
Isolation			4000	VAC	For 1 min. Double/reinforced with a working voltage of 250 VAC. Meets 2 x MOPP per 3rd edition of IEC60601-1 5000 VAC for 10 ms in accordance with IEC60664-1
Input to Output Capacitance			20	pF	
Switching Frequency		250		kHz	
Power Density			23	W/in ³	
Mean Time Between Failure		>1		MHrs	MIL-HDBK-217F, +25 °C GB
Weight		0.04 (20.0)		lb (g)	

Environmental						
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Operating Temperature	-40		+80	°C	See derating curve	
Storage Temperature	-55		+100	°C		
Case Temperature			+100	°C		
Humidity	5		90	%RH	Non-condensing	
Cooling					Natural convection	
Shock	±3 shocks in each plane, total 18 shocks of 30 g : 11 ms halfsine. Conforms to EN60068-2-27 & EN60068-2-47					
Vibration	10-500 Hz at 2 g sweep and endurance at resonance in all 3 planes. Conforms to EN60068-2-6					

JHM15 Series



EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55011 & EN55022	Level A	
Radiated	EN55011 & EN55022	Level A	

EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions		
Immunity	IEC60601-1-2, EN61204-3					
ESD Immunity	EN61000-4-2	2	A			
Radiated Immunity	EN61000-4-3	10 V/m	A			
EFT/Burst	EN61000-4-4	2	A			
Surges	EN61000-4-5	1	A			
Conducted Immunity	EN61000-4-6	10 Vm	A			
Magnetic Fields	EN61000-4-8	3 A/m	A			
Safety Approvals	ANSI/AMMI ES60601-1 3rd Edition, CSA-22.2 No.60601-1:2008, IEC60601-1 3rd Edition					

UL

Safety Standard

IEC60601-1 Ed 3 Including Risk Management

ANSI/AAMI ES60601-1 3rd Ed. & CSA C22.2, No.60601-1:2008


Safety Approvals

Safety Agency


CB Report

Application Notes

Derating Curve



External Output Trim



For 5 V output: Trim +10%, R = 3.4 k typical Trim -10%, R = 1.1 k typical

For 12 V output: Trim +10%, R = 5.9 k typical Trim -10%, R = 11.3 k typical

For 15 V output: Trim +10%, R = 8.4 k typical Trim -10%, R = 10.4 k typical For ± 5 V output: Trim +10%, R = 12.0 k typical Trim -10%, R = 8.0 k typical

Notes & Conditions

Medical

Medical

For ± 12 V output: Trim +10%, R = 12.8 k typical Trim -10%, R = 9.5 k typical

For ± 15 V output: Trim $\pm 10\%$, R = 18 k typical Trim $\pm 10\%$, R = 14.8 k typical

www.xppower.com