



Technical data

4T-09067/09195


Single row tapered roller bearings

Tapered roller bearing, pressed steel cage


KIT CONTENT

4T-09195, 4T-09067

VISUAL (S)



4T-09067/09195
Single row tapered roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	19,05 mm
D - External diameter	49,225 mm
B - Bearing/Inner ring width	19,05 mm
C - Outer ring width	14,288 mm
T - Total width	18,034 mm
d1 - External diameter inner ring	32,5 mm
a - Charge load application point	10,434 mm
Mass	0,179 kg

PRODUCT PERFORMANCE

C - Dynamic load	42,5 kN
C0 - Static load	39 kN
Cu - Fatigue limit load	4,75 kN



PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.27
Y0 - Static axial load coefficient	1.24
Y2 - Upper axial load coefficient	2.26
N lim - Oil lubrication limit speed	11000 tr/min
N lim - Grease lubrication limit speed	8500 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	24 mm
db min - Min IR shoulder diameter	25,5 mm
Da max - Max shoulder diameter OR	42 mm
Db min - Min OR shoulder diameter	44,5 mm
ra max - Max fillet radius	1,3 mm
r1a - Max fillet radius	1,3 mm

KIT COMPONENT

Cone designation	4T-09067
Cup designation	4T-09195

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-09067/09195
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material

Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

Fa / Fr ≤ e		Fa / Fr > e	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X _o	Y _o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table

