

Housing - HC-D 25-TFL-58/O1PG16G - 1672819

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sleeve housing, for single locking latch, height 58 mm, without screw connection, 1x Pg16, straight cable entry

The illustration shows version HC-D 25-TFL-72/M 1 PG 16 G



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 145347
Weight per Piece (excluding packing)	117.29 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	58 mm
Width	36 mm
Length	79.5 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D25, A16
Type	D25
Housing type	Sleeve housings
Locking type	for single locking latch
No. of cable exits	1
Cable exit	Straight
Screw connection	none

Housing - HC-D 25-TFL-58/O1PG16G - 1672819

Technical data

General

Type of the screw connection	1x Pg16
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Housing - HC-D 25-TFL-58/O1PG16G - 1672819

Approvals

Approval details

GOST 

Drawings

Dimensioned drawing

