

FEATURES

- Hexagonal drive type
- Allows for unimpeded mechanical operation
- Generally non-magnetic
- Set screws to DIN916 standards
- Supplied in a polypropylene case

800 piece Stainless Steel Screw/Bolt Kit, M3, M4

RS Stock No.: 395-428



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted professional brand, RS PRO, this set of high-quality hexagon socket set screws are ideal for many applications in which a screw or bolt head would be detrimental to the overall operation. These fasteners usually have an entirely threaded body without a protruding head, although this is present on some styles, and an internal wrenching drive or Allen key is required to secure these screws into place. Once fastened, the set screw exerts a clamping force in order to secure the joined components in place by providing friction.

General Specifications

Number Of Pieces	800
Screw/Bolt Type	Set Screw
Head Shape	Hex
Drive Type	Hexagon Socket
Kit Contents	M3 x 3 Quantity- 100 M3 x 6 Quantity- 100 M3 x 12 Quantity- 50 M4 x 4 Quantity- 50 M4 x 6 Quantity- 100 M4 x 12 Quantity- 100 M5 x 5 Quantity- 50 M5 x 8 Quantity- 50 M5 x 10 Quantity- 50 M6 x 6 Quantity- 50 M6 x 8 Quantity- 50 M6 x 12 Quantity- 50
Applications	Cladding and roofing, Metal (including steel) and wood frames, Car production lines, Sheet metal work

Mechanical Specifications

Screw/Bolts Lengths	3mm to 12mm
Thread Size	M3, M4
Material	Stainless Steel
Stainless Steel Type	304, A2
Finish	Plain
Screw/Bolt Length Longest	12mm
Screw/Bolt Length Shortest	3mm
Specification	DIN 916



3 x 6 RS 137-720	3 x 3 RS 137-714	4 x 6 RS 137-758	4 x 12 RS 137-764
3 x 12 RS 137-736	4 x 4 RS 137-742	5 x 5 RS 137-770	5 x 8 RS 137-786
6 x 8 RS 137-821	6 x 6 RS 137-815	6 x 12 RS 137-837	5 x 10 RS 137-792

Kit Contents			
Size	Quantity	Size	Quantity
M3 x 3	100	M5 x 5	50
M3 x 6	100	M5 x 8	50
M3 x 12	50	M5 x 10	50
M4 x 4	50	M6 x 6	50
M4 x 6	100	M6 x 8	50
M4 x 12	100	M6 x 12	50