



Product data sheet

Power tools for trade & industry

Cordless Impact Drill/Drivers

PRO GSB 18V-25



Make tough jobs easier – with the versatile 18V cordless impact drill driver

The most important data

Torque (soft/hard/max.)	21/56/60 Nm
No-load speed (1st gear / 2nd gear)	0 – 440 / 0 – 1,650 rpm
Battery voltage	18.0 V

Part Number 0 601 9K9 377

Technical data

Technical data

Torque (soft/hard/max.)	21/56/60 Nm
No-load speed (1st gear / 2nd gear)	0 – 440 / 0 – 1,650 rpm
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18.0 V
Weight excl. battery	1.2 kg
Packaging dimensions (width x length x height)	389 x 440 x 145 mm
Chuck type	Keyless chuck
BITURBO	No
Work light	+
Tool design	Pistol

Noise/vibration information

Drilling in metal

Vibration emission value ah	1 m/s ²
Uncertainty K	1.5 m/s ²

Impact drilling in masonry

Vibration emission value ah	12.8 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cordless for maximum freedom, convenience, and safety
- Suitable for a range of applications, even masonry, due to impact drilling function Electronic features protect the motor and extend the battery life
- Compatible with all Bosch 18V batteries and chargers
Ideal for driving screws into wood and drilling into masonry, metal, and wood



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

