



## 23220CE4

### Spherical Roller Bearings

#### Boundary Dimensions


d	100	mm	Bore diameter
D	180	mm	Outside diameter
B	60.3	mm	Width
r (min.)	2.1	mm	Chamfer dimension

#### Basic Load Ratings

Cr	525000	N	Basic dynamic load rating
C0r	605000	N	Basic static load rating

#### Speeds

Thermal Speed Rating (Oil-bath)	2800	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	3800	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1600	min-1	Grease lubrication
Oil (Oil-bath)	2200	min-1	Oil-bath lubrication



#### Abutment and Fillet Dimensions

da (min.)	112	mm	Diameter of shaft abutment
da (max.)	118	mm	Diameter of shaft abutment
Da (min.)	155	mm	Diameter of housing abutment
Da (max.)	168	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

#### Calculation factors

e	0.32	Constant
Y2	3.2	Axial load Factors
Y3	2.1	Axial load Factors
Y0	2.1	Axial load Factors

#### Mass

Mass approx.	6.6	kg	Mass approx.
--------------	-----	----	--------------

