



AMP

TE Internal #: 2101553-1

7 Position Circular Connector, Wire-to-Panel, Sealable, Reverse Gender, Black Chromium, Copper Alloy, PEEK, 2 Shell Size, Contacts Preloaded

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 7

Connector System: **Wire-to-Panel**

Sealable: **Yes**

Reverse Gender: **Yes**

Shell Plating Material: **Black Chromium**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Panel
Sealable	Yes
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Number of Positions	7
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	875 VAC
-------------------	---------

Body Features

Environmental Protection Type	Sealed
Environmental Protection	With
Shell Plating Material	Black Chromium
Shell Base Material	Copper Alloy
Circular Connector Insulation Material Type	PEEK

Contact Features

Reverse Gender	Yes
----------------	-----



Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket

Mechanical Attachment

Panel Mount Feature Type	Flange
Mating Retention Type	Threaded Coupling
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	2
-------------------------------	---

Dimensions

Panel Thickness (Recommended)	3 mm[.118 in]
Assembly Length	23.64 mm

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	10
--------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (1.55% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with tin/lead solder



Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2101550-2
PLUG,7 POS,Sz103,w/SOLDER CUPS,
240 POT


Customers Also Bought




TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING




TE Part #281934-2
SINGLE WIRE SEAL




TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts




TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT

Documents

Product Drawings
PLUG,7 POS,CIRCULAR HD,PCB-POL2
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2101553-1_C_c-2101553-1-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2101553-1_C_c-2101553-1-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2101553-1_C_c-2101553-1-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English