



ENGLISH

Datasheet

Aluminium Electrolytic Capacitor

RS Stock number 711-1696




Specifications:

Item	Performance Characteristics																																												
Operating Temperature Range	-40 to +105°C	-25 to +105°C																																											
Rated Voltage Range	6.3 to 100 VDC	160 to 450 VDC																																											
Capacitance Tolerance	± 20% (120Hz, +20°C)																																												
Leakage Current (at 20°C, max.)	I < 0.01 CV or 3 (µA). After 1 minute whichever is greater measured with rated working voltage applied.	I < 0.03 CV or 3 (µA). After 1 minute with rated working voltage applied.																																											
Dissipation Factor (120Hz, 20°C)	<table border="1"> <tr> <td>Working voltage (VDC)</td> <td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>100</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td> </tr> <tr> <td>D.F (%) Max.</td> <td>23</td><td>20</td><td>16</td><td>14</td><td>12</td><td>10</td><td>10</td><td>10</td><td>15</td><td>15</td><td>16</td><td>20</td><td>20</td><td>20</td> </tr> </table>															Working voltage (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450	D.F (%) Max.	23	20	16	14	12	10	10	10	15	15	16	20	20	20
	Working voltage (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450																														
D.F (%) Max.	23	20	16	14	12	10	10	10	15	15	16	20	20	20																															
For capacitance > 1000µ F, add 2% per another 1000µ (+20°C at 120Hz)																																													

Specifications:

Item	Performance Characteristics																																													
Low Temperature Characteristics (at 120Hz)	Impedance ratio max.																																													
	<table border="1"> <thead> <tr> <th>W.V (VDC)</th> <th>6.3</th> <th>10</th> <th>16</th> <th>25</th> <th>35</th> <th>50</th> <th>63</th> <th>100</th> <th>160</th> <th>200</th> <th>250</th> <th>350</th> <th>400</th> <th>450</th> </tr> </thead> <tbody> <tr> <td>Z-25°C/+20°C</td> <td>4</td> <td>3</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>3</td> <td>3</td> <td>3</td> <td>5</td> <td>6</td> <td>15</td> </tr> <tr> <td>Z-40°C/+20°C</td> <td>9</td> <td>6</td> <td>4</td> <td>4</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>-</td> <td>-</td> <td>-</td> <td>-</td> <td>-</td> <td>-</td> </tr> </tbody> </table>	W.V (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450	Z-25°C/+20°C	4	3	2	2	2	2	2	2	3	3	3	5	6	15	Z-40°C/+20°C	9	6	4	4	3	3	3	3	-	-	-	-	-	-
	W.V (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450																															
Z-25°C/+20°C	4	3	2	2	2	2	2	2	3	3	3	5	6	15																																
Z-40°C/+20°C	9	6	4	4	3	3	3	3	-	-	-	-	-	-																																
For capacitance value 1000µF, add 0.5 per another 1000µF for -25°C/+20°C For capacitance value 1000µF, add 1 per another 1000µF for -40°C/+20°C																																														
Load Life	Test Conditions: Duration time: 2000hrs Ambient temperature: +105°C Applied voltage: Rated DC working voltage After test requirements: +20°C After test requirements: ≤ ± 20% of initial measured value Dissipation Factor: ≤ 200% of the initial specified value Leakage Current: ≤ the initial specified value																																													
Shelf Life	Test Conditions: Duration time: 1000hrs Ambient temperature: +105°C Applied Voltage: None After test requirements at +20°C: Same limits as load life. Pre-treatment for measurements shall be conducted after application of DC working voltage for 30 minutes.																																													

Diagram of Dimensions:



	(Unit: mm)									
D	5	6	8	10	13	16	18	22	25	
F	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10	12	
ϕd	0.5			0.6			0.8			1.0

**Features:**

- Used in communication equipment's, switching power supply, etc.
- Safety vent construction design

Ripple Current & Temperature

Temperature (°C)	45	60	70	85	105
Multiplier	2.10	1.90	1.65	1.40	1.00

Ripple Current & Frequency Multipliers

CAP (μF)/Hz	50 (60)	120	400	1K	10K	50 – 100K
CAP ≤ 10	0.8	1.0	1.30	1.45	1.65	1.70
10 < CAP ≤ 100	0.8	1.0	1.23	1.36	1.48	1.53
100 < CAP ≤ 1000	0.8	1.0	1.16	1.25	1.35	1.38
1000 < CAP	0.8	1.0	1.11	1.18	1.25	1.28

Case Size

Ø D x L (mm)

WV (SV) uF	6.3		{8}		10		{13}		16		{20}		25		{32}		35		{44}	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
4.7													5x11	27	5x11	29				
6.8													5x11	35	5x11	38				
10									5x11	38			5x11	40	5x11	42				
22			5x11	50					5x11	56			5x11	60	5x11	62				
33	5x11	56	5x11	60					5x11	65			5x11	70	5x11	78				
47	5x11	68	5x11	72					5x11	100			5x11	105	5x11	110	5x11	115		
68	5x11	77	5x11	82					5x11	105			6.3x11	120	6.3x11	140				
100	5x11	98	5x11	110					5x11	115	6.3x11	135	6.3x11	150	6.3x11	165	6.3x11	180		
220	5x11	180	6.3x11	180					6.3x11	220	8x11	230	8x11	240	8x11	300	8x11	330		
330	6.3x11	200	6.3x11	260	8x11	280			8x11	300			8x11	350	10x12	410	10x12	420		
470	6.3x11	280	6.3x11	300	8x11	315			8x11	380	10x12	400	8x14	415	10x17	480	10x12	520		
560	8x11	320	8x11	330	10x12				10x12	410			10x15	460	10x17	540				
680	8x11	360	10x12	420	10x12				10x12	480			10x15	520	10x20	650				
820	8x11	390	10x12	480	10x15				10x15	550			10x15	640	10x20	760				
1000	8x11	420	10x12	530	8x16	10x15	570	600	10x15	740	10x17	850	10x20	740	10x25	870	10x17	880		
1200	10x15	480	10x15	650	10x17				10x20	710			10x20	850						
1500	10x15	620	10x17	770	10x20				10x20	820			13x21	910	13x26	970				
2200	10x17	780	10x17	870	13x21	1020			13x21	1060	13x26	1080	13x21	1210	16x26	1300	13x26	1400		
2700	10x20	850	13x21	920	13x21				13x21	1100			16x26	1330	16x31	1500				
3300	10x20	970	10x25	1110	13x21	1220			13x21	1240	13x26		16x26	1480	16x36	1680	16x26			
4700	10x25	1160	13x21	1380	16x26				16x26	1620			16x31	1800	18x36	1900	16x31			
5600	13x26	1320	16x26	1510	16x31				16x31	1720			16x36	1890	18x36	2000	16x36			
6800	16x26	1470	16x26	1680	16x31				16x31	1880			18x36	2040	18x41	2090	18x36			
8200	16x26	1520	16x31	1840	16x36				16x36	1950			18x36	2090	22x42	2180	18x36			
10000	16x26	1690	16x36	1900	18x36	2080			18x41	2080			22x42	2200	25x44	2300	22x42			
15000	16x36	2080	18x36	2230	22x40				22x40	2300			22x42	2500	-	-	22x42			

Ripple Current(mA,rms)at105□120Hz

Case Size uF	50 {63}		63 {79}		100 {125}		160 {200}		200 {250}	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
0.1	5x11	1.3	5x11	1.3	5x11	1.3	-	-	-	-
0.22	5x11	2.9	5x11	2.9	5x11	2.9	-	-	-	-
0.33	5x11	4.2	5x11	4.2	5x11	4.2	-	-	-	-
0.47	5x11	8	5x11	8	5x11	8	5x11	12	5x11	12
1	5x11	14	5x11	14	5x11	15	5x11	17	6.3x11	17
2.2	5x11	20	5x11	21	5x11	22	6.3x11	28	6.3x11	33
3.3	5x11	26	5x11	28	5x11	30	6.3x11	32	6.3x11	43
4.7	5x11	32	5x11	34	5x11	36	6.3x11 8x11	36 42	8x11	51
6.8	5x11	40	5x11	42	6.3x11	47	8x11	56	10x12	63
10	5x11	50	5x11	51	6.3x11	60	8x11 10x12	75 78	10x12 10x15	83 90
22	5x11	75	5x11 6.3x11	75 85	6.3x11 8x11	98 105	10x15	105	10x20	135
33	5x11 6.3x11	90 95	6.3x11 8x11	105 115	8x11 10x12	145 155	10x20	170	13x21	180
47	6.3x11	120	6.3x11 8x11	145 155	10x12 10x15	170 180	13x21	210	13x21 13x28	220 230
68	8x11	155	8x11	185	10x15	240	13x28	280	16x28	300
100	8x11	200	10x12	240	10x20	290	13x28 16x28	320 330	16x28	360
220	10x12 10x15	350 380	10x17 10x20	400 430	13x28 16x28	530 560	16x38	580	18x38	590
330	10x17 10x20	450 470	13x21	570	16x28	680	18x31	710	18x38	740
470	13x21	610	13x21 13x28 16x28	640 700 720	16x28 16x31	840 860	18x41	880	22x42	890
560	13x21	660	13x28	770	16x38	880	-	-	-	-
680	13x28	770	16x28	880	16x38	920	-	-	-	-
820	13x28	850	16x28	920	18x31	970	-	-	-	-
1000	13x28 16x28	900 1010	16x32 16x38	1190 1220	18x41	1250	-	-	-	-
1500	16x31	1300	18x31	1350	22x42	1500	-	-	-	-
2200	18x38	1550	18x38	1590	25x44	1880	-	-	-	-
2700	18x38	1610	22x42	1720	-	-	-	-	-	-
3300	18x38	1780	22x42	1900	-	-	-	-	-	-
4700	22x42	2050	25x44	2200	-	-	-	-	-	-
5600	25x42	2180	-	-	-	-	-	-	-	-
6800	25x44	2280	-	-	-	-	-	-	-	-

Ripple Current(mA,rms)at105□120Hz

Case Size WV {SV}	Ø D x L (mm)															
	250		{300}		350		{400}		400		{450}		450		{500}	
uF	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
0.47	5x11	12	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15
1	6.3x11	17	6.3x11	20	8x11	22	8x11	22	8x11	22	8x11	22	8x11	22	8x11	22
2.2	8x11	36	10x12	39	10x12	39	10x12	39	10x12	39	10x12	39	10x12	39	10x12	39
3.3	8x11	43	10x12	53	10x12 10x15	53	55	55	10x15 10x20	53	55	55	10x15 10x20	53	55	55
4.7	10x12	51	10x12 10x15	63	66	66	66	66	10x15	69	69	69	10x20	64	64	64
6.8	10x12	70	10x15	79	10x15	85	85	85	10x15	85	85	85	10x20	75	75	75
10	10x15	90	10x20	110	10x15 10x20 13x21	100	112	115	13x21 13x26	92	98	98	13x21 13x26	92	98	98
22	10x20	160	13x26	180	13x21 16x26	170	190	190	16x26 16x31	175	180	180	16x26 16x31	175	180	180
33	13x21 13x26	175	180	180	16x26	190	190	190	16x26	220	220	220	16x36	210	210	210
47	13x26	240	16x31	250	16x31	300	300	300	16x31	300	300	300	16x36	280	280	280
68	16x26	320	16x31	330	16x31	330	330	330	16x36	355	355	355	18x36	330	330	330
100	16x31	400	18x36	420	18x36	450	450	450	18x36	450	450	450	-	-	-	-
120									18x31	440	440	440				

Ripple Current(mA,rms)at105□120Hz