



## Main

Device short name	SDx
Product or component type	Auxiliary contact
Range compatibility	Compact VigiCompact NSXm
Signal contacts composition	1 NO/NC for fault 1 NO/NC for alarm

## Complementary

Fault type	Earth leakage Overload
Local signalling	1 LED green for ON status 2 LEDs red for output status
[Ue] rated operational voltage	24...240 V AC/DC
[Ie] rated operational current	Utilisation category AC-15 : 0.3 A network: AC 50/60 Hz at 250 V Utilisation category AC-15 : 1.74 A network: AC 50/60 Hz at 230 V Utilisation category DC-13 : 0.3 A at 160 V Utilisation category DC-13 : 2.08 A at 24 V Utilisation category DC-13 : 5 A at 10 V Utilisation category AC-15 : 5 A network: AC 50/60 Hz at 80 V
Auxiliary connection terminal	Spring 0.5...1.5 mm <sup>2</sup> copper
Wire stripping length	8 mm