

# Angular contact ball bearings 7307-B-XL-MP (Series 73..-B)

main dimensions to DIN 628-1, contact angle  $\alpha = 40^\circ$

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

|                     |          |
|---------------------|----------|
| d                   | 35 mm    |
| D                   | 80 mm    |
| B                   | 21 mm    |
|                     |          |
| a                   | 35 mm    |
| D <sub>1</sub>      | 63,02 mm |
| d <sub>1</sub>      | 53,12 mm |
| D <sub>a max</sub>  | 71 mm    |
| d <sub>a min</sub>  | 44 mm    |
| D <sub>b max</sub>  | 74,4 mm  |
| r <sub>1 min</sub>  | 1 mm     |
| r <sub>a1 max</sub> | 1 mm     |
| r <sub>a max</sub>  | 1,5 mm   |

|           |             |                                   |
|-----------|-------------|-----------------------------------|
| $r_{min}$ | 1,5 mm      |                                   |
| $\alpha$  | 40 °        | Contact angle                     |
| $m$       | 0,475 kg    | Mass                              |
| $C_r$     | 43000 N     | Basic dynamic load rating, radial |
| $C_{0r}$  | 27500 N     | Basic static load rating, radial  |
| $C_{ur}$  | 1910 N      | Fatigue limit load, radial        |
| $n_G$     | 14100 1/min | Limiting speed                    |
| $n_{9r}$  | 7900 1/min  | Reference speed                   |



