Panasonic ideas for life

Panasonic recommends Windows 8.

TOUGHPAD FZ-G1

- MIL-STD-810G, 4ft. Drop and All-weather IP65 Dust and Water-resistant Design
- 3rd Generation Intel[®] Core[™] i5 vPro[™] Processor
- 10.1" Daylight-readable 10-point Multi Touch
 + Digitizer
- USB 3.0 + HDMI Ports, Optional Dedicated GPS, Serial, Ethernet, MicroSD or 2nd USB Port¹
- Wi-Fi, Bluetooth[®] and Optional 4G LTE or 3G Gobi[™]
- □ 3-year Warranty with Business Class Support

The world's thinnest and lightest fully-rugged 10.1" Windows[®] 8 Pro tablet.

The Toughpad[™] FZ-G1 Windows[®] 8 Pro tablet offers a fluid user experience while providing crucial port connectivity and feature rich options in a compact size. Designed for highly mobile field workers, it's the thinnest and lightest fully-rugged 10.1" tablet running Genuine Windows[®] 8 Pro 64-bit. Powered by a 3rd generation Intel[®] Core[™] i5 vPro[™] Processor with a MIL-STD-810G, 4ft. drop and all-weather IP65 dust and water-resistant design, the Toughpad FZ-G1 Windows[®] 8 Pro tablet leads the way in rugged mobile computing. Add to that an HD daylight-readable 10-point multi touch + digitizer screen, and it becomes an essential tool for field workers.



1.800.662.3537 panasonic.com/toughpad



Panasonic recommends Windows 8.

DURABILITY	 MIL-STD-810G design IP65 sealed all-weather design Magnesium alloy chassis encased wi Optional rotating hand strap Port covers Raised bezel for LCD impact protecti Pre-installed replaceable screen film f 	on		
SOFTWARE	 Windows[®] 8 Pro 64-bit (with Windows[®] 7 downgrade option) Panasonic Utilities (including Dashboard), Recovery Partition 			
CPU	 Intel[®] Core[∞] i5-3437U vPro[∞] Processor - 1.9GHz with Turbo Boost up to 2.9GHz - Intel Smart Cache 3MB 		WARRANTY	
STORAGE & MEMORY	 4GB or 8GB^{2,3} Up to 64GB additional with optional microSD card 128GB and 256GB solid state drives (SSD)^{2,3} 		DIMENSIONS & WEIGHT ⁹ = 10.6°(L) × 7.4°(W) × 0.8°(H) = 2.5 lbs.	
DISPLAY	 10.1" WUXGA 1920 x 1200 with LED backlighting 10-point capacitive multi touch + digitizer daylight-readable screen 2-800 nit IPS display with direct bonding Anti-reflective and anti-glare screen treatments Ambient light sensor, digital compass, gyro and acceleration sensors Automatic screen rotation Intel[®] QM77 video controller, max. 1664MB shared VRAM with Win 8 64-bit⁴ 		INTEGRATED OPTIONS ¹⁰ ■ 4G LTE mobile broadband ⁶ ■ 3G Gobi [™] mobile broadband ⁶ ■ Choice of GPS, Serial, Ethernet, MicroSD or 2nd USB 2.0 port ⁹ ACCESSORIES ¹⁰ ■ AC Adapter (3-prong) CF-AA6413CM	
AUDIO	 Integrated microphone Realtek high-definition audio Integrated speaker On-screen and button volume and mute controls 		Standard Battery Pack FZ-VZ3 Long Life Battery Pack FZ-VZ3 Rotating Hand Strap FZ-WS Replacement Digitizer Stylus Pen FZ-WU Tall Corner Guards FZ-WC	46413CM SU84U SU88U IPG111 IPG11U CGG111 BG11U
KEYBOARD & INPUT	 10-point multi touch + digitizer screen Supports bare hand touch and gestures and electronic stylus pen 7 tablet buttons (2 user-definable) Integrated stylus holder On-screen QWERTY keyboard 			
CAMERAS	 720p webcam with mic 3MP rear camera with auto focus and LED light 			
EXPANSION	Optional MicroSD ¹			
INTERFACE	 Docking connector HDMI Headphones/speaker Optional Serial¹ USB 3.0 (x 1) Optional 2nd USB 2.0¹ Optional 10/1000 Ethernet¹ 	24-pin Type A Mini-jack stereo D-sub 9-pin (available Spring 2013) 4-pin 4-pin RJ-45		
WIRELESS	 Optional integrated 4G LTE mobile broadband⁶ Optional integrated 3G Gobi¹⁷ mobile broadband⁶ Optional dedicated GPS (available Summer 2013)¹ Intel[®] Cartino[®] Advanced-N 6235 WI-FI 802.11a/b/g/n Bluetooth[®] v4.0 (Class 1) + EDR Security Authentication: LEAP, WPA, 802.1x, EAP-TLS, EAP-FAST, PEAP Encrybion: CKIP, TKIP, 128-bit and 64-bit WEP, Hardware AES Dual high-gain antenna pass-through 		Please consult your reseller or Panasonic representative before pu	urchasing.
POWER SUPPLY	 Li-lon battery pack (10.8V, typical 4400mAh, minimum 4100mAh) Battery operation: Approx. 8 hours' Battery charging time: 2.5 hours off, 3 hours on' AC Adapter: AC 100V-240V 50/60Hz 		Caution: Do not expose bare skin to this product when handling this unit in extreme hot or cold environments. 'GPS, Serial, Ethernet, MicroSD, 2nd USB port are mutually exclusive options. '1GB = 1,000,000,000 bytes. ''Total usable memory will be less depending upon actual system configuration. 'The size of the VFAM cannot be set by the user and varies by operating system as well as size of RAM. Windows 7 max. VFAM is 1544/MB.	
POWER MANAGEMENT	Suspend/Resume Function, Hibernation, Standby			iery performance features
SECURITY FEATURES	 Password Security: Supervisor, User, Kensington cable lock slot Trusted platform module (TPM) secur Computrace[®] theft protection agent in Intel[®] Anti-Theft Technology Optional SmartCard reader (separate 	ity chip v.1.2 n BIOS [®]	such as charge time and life span can vary according to the conditions under which the computer and battery are used. Battery operation and recharge times will vary based on many factors, including screen brightness, applications, features, power management, battery conditioning and other customer preferences. Battery testing results from MobileMark 2007. "Requires software and activation to enable theft protection. "Length measurements do not include protrusions. Weight varies with options and digitizer pen "Accessories and Integrated Options may vary depending on your configuration. Visit Panasonic website for more accessories and details.	

1.800.662.3537 panasonic.com/toughpad Panasonic is constantly enhancing product specifications and accessories. Specifications subject to change without notice. Trademarks are property of their respective owners. ©2013 Panasonic Corporation of North America. All rights reserved. SS_TPG1_02/13

