



STANLEY® FATMAX® HEAVY DUTY TRADE KNIFE - Black



FMHT10505-0 - STANLEY® FATMAX® HEAVY DUTY TRADE KNIFE - Silver

- IMPROVED THUMB WHEEL - Helix screw on thumb wheel allows fewer rotations of the wheel to open the knife creating faster blade change
- DUAL MAGNETIC BLADE STORAGE - Divided magnetic blade storage allows the user to access two types of blades quickly without them falling out when the knife is opened
- THUMB WHEEL ACCESSIBILITY - More pronounced, and accessible thumb wheel allows user to open and close knife faster and easier
- REDESIGNED HANDLE CONTOUR - New geometry with less aggressive flare keeps hand from sliding backwards and keeps hand in optimal position for cutting
- IMPROVED HANDLE - New H handle design with 'N' texture and softer cross-sections, Improves comfort, reduces the chance of slipping when in use, and provides more control while cutting.
- KNURLING - Added Knurling texture on nose provides a 'landing spot' for fulcrum allowing the user to have more control while making precision cuts.
- MAGNET FOR BLADE RETENTION AND MINIMAL BLADE DEFELECTION - Hardened Steel blade holder to reduce nose wear

Knife Holster - Yes

Supplied with: 2 x straight blades and 1 x hooked

If your STANLEY product becomes defective due to faulty materials or workmanship within 12 months from the date of purchase, STANLEY guarantees to replace all defective parts free of charge or – at our discretion – replace the unit free of charge. See <https://www.2helpu.com/STANLEY> for more information.