


# Product datasheet

Specifications



## Mechanical and electrical interlock, TeSys D reversing & changeover, 2 contactors LC1D115-D150

Local distributor code:

386285280

LA9D11502

EAN Code: 3389110859485

### Main

Range of product	TeSys Deca
Range	Lineryg
product name	FT
Device short name	LA9D
Product or component type	Mechanical interlock
Accessory / separate part category	Interlocking accessory
Interlocking type	Electrical and mechanical
Poles description	3P 4P
Electrical circuit type	Changeover Reversing
Range compatibility	TeSys TeSys D contactor TeSys TeSys Deca
Product compatibility	LC1D115 LC1D150

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.200 cm
Package 1 Width	9.600 cm
Package 1 Length	23.000 cm
Package 1 Weight	281.000 g
Unit Type of Package 2	S06
Number of Units in Package 2	105
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	44.080 kg

### Logistical informations

Country of origin	CZ
-------------------	----

### Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.



[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant
China RoHS Regulation	<a href="#">China RoHS declaration</a>

Use Again

 Repack and remanufacture	
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No