

Product datasheet

Specifications



CLIP IN MARKING STRIP, 5MM, 10 STRIPS, PRINTED CHARACTERS L1,L2,L3, N

Local distributor code:
397161403

NSYTRAB5L1N

EAN Code: 3606480535413

Main

product name	Linergy TR
Range	Linergy
Product or component type	Marking strip
Device short name	TRA
Accessory / separate part category	Marking accessory
Product compatibility	Terminal block
Background colour	White
Marking	N L1 - L2 - L3 PE
Size	5 mm
Quantity per set	Set of 10

Complementary

Type of marking	Symbolic
Colour of marking	Black
Material	Polyamide 6/6
Product weight	1.07 g

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	5.000 cm
Package 1 Length	2.330 cm
Package 1 Weight	0.900 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	1.500 cm
Package 2 Width	5.000 cm
Package 2 Length	7.000 cm
Package 2 Weight	14.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 3	S02
Number of Units in Package 3	900
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.574 kg

Logistical informations

Country of origin	DE
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.


[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
China RoHS Regulation	China RoHS declaration
Silicon free	Yes

Use Again

 Repack and remanufacture	
Halogen content performance	Halogen free plastic parts product
Take-back	No