

## Printed-circuit board connector - DFK-PCV 5/ 9-GF-7,62 - 1716467

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 41 A, Rated voltage (III/2): 630 V, Number of positions: 9, Pitch: 7.62 mm, Color: green, Contact surface: Tin, Mounting: Soldering



The figure shows a 5-pos. version of the product

### Why buy this product

- ☒ Panel thickness of 1 mm to 3 mm
- ☒ For soldering onto the PCB
- ☒ Mounted on the housing panel by means of tool-free snap-lock mechanism or conventional screw connection
- ☒ Feed-through headers for use in combination with all PC 5 plugs



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 10 pc                                                                                                   |
| Minimum order quantity               | 10 pc                                                                                                   |
| GTIN                                 | <br>4 046356 137089 |
| Weight per Piece (excluding packing) | 26.43 g                                                                                                 |
| Custom tariff number                 | 85366990                                                                                                |
| Country of origin                    | Poland                                                                                                  |
| Note                                 | Made to Order (non-returnable)                                                                          |

### Technical data

#### Dimensions

|                |           |
|----------------|-----------|
| Length         | 19.54 mm  |
| Pitch          | 7.62 mm   |
| Dimension a    | 60.96 mm  |
| Pin dimensions | 0,8 x 1,0 |
| Pin spacing    | 7.62 mm   |
| Hole diameter  | 1.3 mm    |

#### General

|                   |                 |
|-------------------|-----------------|
| Range of articles | DFK-PCV 5/..-GF |
|-------------------|-----------------|

# Printed-circuit board connector - DFK-PCV 5/ 9-GF-7,62 - 1716467

## Technical data

### General

|                                         |        |
|-----------------------------------------|--------|
| Insulating material group               | I      |
| Rated surge voltage (III/3)             | 6 kV   |
| Rated surge voltage (III/2)             | 6 kV   |
| Rated surge voltage (II/2)              | 6 kV   |
| Rated voltage (III/3)                   | 500 V  |
| Rated voltage (III/2)                   | 630 V  |
| Rated voltage (II/2)                    | 800 V  |
| Connection in acc. with standard        | EN-VDE |
| Nominal current $I_N$                   | 41 A   |
| Maximum load current                    | 41 A   |
| Insulating material                     | PA     |
| Inflammability class according to UL 94 | V0     |
| Color                                   | green  |
| Number of positions                     | 9      |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27141190 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

## Approvals

### Approvals

# Printed-circuit board connector - DFK-PCV 5/ 9-GF-7,62 - 1716467

## Approvals

Approvals

EAC

Ex Approvals


Approvals submitted

Approval details


EAC

## Drawings

Drilling diagram




Dimensioned drawing



Sheet metal cutout for snap-on.

Dimensioned drawing



Sheet metal cutout for screw connection.

Dimensioned drawing

