

Angle drill LXT®

DDA450

18V • 70 Nm • 0 – 1 400 min⁻¹

LXT® powered angle drill for tight spaces

Compact and lightweight for increased maneuverability in various work postures and reduced user fatigue. High-speed drilling beyond AC powered tool.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	0 - 450 / 1400 min ⁻¹
Max. Drilling Diameter in Wood	38 mm
Max. Drilling Diameter in Steel	13 mm
Driving Shank	1/2"-20UNF "
Drill Chuck Capacity	1,5 - 13 mm
Angle length	179 mm
Max. Torque (2. Gear / 1. Gear)	26 / 70 Nm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	50 / 65 mm
Vibration Level, Drilling into metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Drilling into metal	1,5 m/s ²
Sound Power Level (L _{WA})	94 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)

User benefits

- Powerful drilling even large diameter holes
- Exceptional high power and high speed
- Ergonomic soft grip handle provides increased comfort
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitaauk.com



Related products

Other

User manual

Parts drawing