

2U and 4U Wall Mount Bracket



2U and 4U Wall Mount Brackets (MCMpan, MCMpan4)

These 2U and 4U 19" wall mount equipment rack brackets offer a versatile storage solution for telephone systems, network devices, power strips and patch panels to be mounted vertically (flush with wall) to save space. Alternatively, these brackets can be installed horizontally under a desk or shelf, making it easy to access installed equipment directly from your workspace.

Features

- Mount server, network or telecommunications devices vertically with this wall mountable rack
- Equipment can be wall mounted vertically or horizontally
- Compatible with most 19" rack mountable equipment
- Wall mounting holes provide great stability and mounting into standard wall studs
- Made from solid steel for durability
- Supplied with cage nuts and wall fixtures for easy equipment mounting

Specifications

- Weight: MCMpan: 600g MCMpan4: 946g
- Dimensions: MCMpan: 505x101.5x99.5mm (Packaged) MCMpan4: 537x262 x155mm (Packaged)
- Material: steel, panel: approx. 1.8mm thick
- Finish: powder painted black

Packaging: in individual poly bag then in individual carton


EAN: MCMpan: 5055386511553

MCMpan4: 5055386511560

Commodity Code: 85381000




Country of Origin: China

Illustrative images – MCMPAN



ROHS Compliant

Code: MCMpan



A-A