



Technical data

KR16FLL/3AS

Cam follower with shaft



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
D - External diameter	16 mm
d1 - Stud diameter	6 mm
C - Width of bearing, drawn cup or outer ring	11 mm
F - Under roller diameter	8 mm
B - Bearing/Inner ring width	12 mm
B1 - Total stud length	28 mm
B2 - Stud rod length	16 mm
G - Stud thread designation	M6X1



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

G1 - Thread length of the stud	8 mm
C1 - Distance between roller face and washer face	0,6 mm
n - Axial lubrication hole diameter	4 mm
e - Inlet diameter of roller or washer	12 mm
R - Track roller radius	500 mm
Maximum tightening torque	3 N-m
Bearing with/without cage	Avec
Radial clearance class	CN
Precision class	P0
Mass	0,019 kg

PRODUCT PERFORMANCE

Cr - Dynamic load rating	4,05 kN
C0r - Static load rating	4,2 kN
Track load capacity spherical outer ring	1,08 kN
N lim - Grease lubrication limit speed	10000 tr/min
Tmin - Min operating temperature	-20 °C
Tmax - Max operating temperature	100 °C

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	KR16FLL/3AS
Image	NRBKR_LL_1.jpg, NRBKR_LL_3.jpg
Rolling element material	Acier 100Cr6

