






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00	B1		REVISED PER ECO-11-004835	11MAR11	RK HMR

- 1 MATERIAL: HOUSING : POLYESTER, GRAY. UL 94V-0.
CONTACT: HIGH CURRENT COPPER ALLOY.
- 2 FINISH: CONTACT MATING AREA: 1.27µm MIN GOLD OR 0.08µm MIN GOLD
OVER 0.76µm PALLADIUM-NICKEL.
ACTION PIN AREA, 0.5µm MIN MATTE TIN PLATE,
ALL OVER 1.27µm MIN NICKEL UNDERPLATE.
- 3 TOLERANCE TO BE ±0.28 AFTER CONNECTOR IS APPLIED TO PC BOARD.
- 4 DATE CODE THIS APPROXIMATE AREA, OPPOSITE SIDE.
- 5 REFERENCE APPLICATION SPEC 114-1103 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
6. CURRENT RATING 16A/CONTACT PER PRODUCT SPEC 108-1651.
- 7 FINISH: CONTACT LUBRICATION WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: GR-1217-CORE ISSUE 1, NOVEMBER 1995.



RECOMMENDED PCB HOLE LAYOUT

12	36.5	11	120953-9
11	33.5	10	120953-8
10	30.5	9	120953-7
9	27.5	8	120953-6
8	24.5	7	120953-5
7	21.5	6	120953-4
6	18.5	5	120953-3
5	15.5	4	120953-2
4	12.5	3	120953-1

POSITION B REF A PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B CARBO 130CT04	TE Connectivity	
		CHK R PATTERSON 130CT04		
DIMENSIONS: mm		APVD R PATTERSON 130CT04	NAME	
		PRODUCT SPEC	RECEPTACLE ASSEMBLY, UNIVERSAL POWER MODULE	
		APPLICATION SPEC		
MATERIAL 1		WEIGHT	SIZE CAGE CODE DRAWING NO	
			A1 00779 120953	
			RESTRICTED TO	
			CUSTOMER DRAWING	
			SCALE 10:1 SHEET 1 OF 1 REV B1	