

Data sheet

Hydraulic data

Maximum operating pressure P_N	10 bar
Head max H_{max}	7.0 m
Minimum suction head at 50 °C m	3 m
Minimum suction head at 95 °C m	10 m
Minimum suction head at 110 °C	16 m
Min. fluid temperature T_{min}	-20 °C
Max. fluid temperature T_{max}	110 °C
Min. ambient temperature T_{min}	-20 °C
Max. ambient temperature T_{max}	40 °C

Materials

Pump housing	Cast iron
Impeller	PPE/PS-GF30
Shaft	Stainless steel
Bearing	Carbon, metal-impregnated

Installation dimensions

Pipe connection on the discharge side DNd	DN 32
Pipe connection on the suction side DNs	DN 32
Port-to-port length Lo	220 mm

Motor data

Energy efficiency index (EEI)	0.23
Mains connection	1~230 V ±10%, 50/60 Hz
Min current I_{min}	0.08 A
Max current I_{max}	1 A
Rated power P_2	90 W
Min. speed n_{min}	1000 1/min
Max. speed n_{max}	3700 1/min
Power consumption $P_{1 min}$	5 W
Power consumption $P_{1 max}$	120 W
Interference emission	EN 61800-3;2004+A1;2012 /residential area (C1)
Interference immunity	EN 61800-3;2004+A1;2012 /industrial environment (C2)
Threaded cable connection	2 x M20x1.5
Insulation class	F
Protection class	IPX4D