

Powerfit™



Industrial Batteries – Powerfit S300
Compact energy for more security.

EXIDE
TECHNOLOGIES


Energy source with high performance and all-round qualities.

Specifications

- Rechargeable VRLA-batteries with an electrolyte retained in a glass mat with a very fine glass-fibre structure
- Perfect combination between energy storage performance and reliability
- Maintenance-free during their whole service life
- Nominal capacity from 1,2 up to 65 Ah
- 5 years design life at 20°C ambient temperature (80% remaining capacity)
- Grid plate construction consisting of a lead calcium alloy
- Low gas emission due to high gas recombination rate of 99%
- Low self-discharge rate (about 3%/month at 20°C)
- Proof against deep discharge according to DIN 43 539 T5
- Trouble-free transportation of operational blocs, no restrictions for most road, rail, air and sea transportation (IATA, DGR clause A 67)
- Completely recyclable



G terminal





S terminal



Applications

As well as their suitability for general applications in security systems, the Powerfit S300 can be a reliable energy source for emergency lighting.



Technical characteristics and data

Standard

Type	Part number	Nominal voltage	Capacity			Length ⁽¹⁾ x Width ⁽¹⁾ x Height ⁽²⁾			Weight approx. kg	Internal resistance mΩ	Max. dis. current A	Terminal	Terminal position					
			C 20	C 10	C 1													
			1,75VpC 20°C	1,75VpC 20°C	1,6VpC 20°C	mm	mm	mm										
V		Ah	Ah	Ah														
S306/1.2 S	NAS30601D2VW0SC	6	1.2	1.10	0.70	97	25	56	0.30	65	18	Faston 4.8	2					
S306/4 S	NAS306004VW0SC	6	4.0	3.80	2.40	70	47	106	0.85	25	60	Faston 4.8	1					
S306/7 S	NAS306007VW0SC	6	7.0	6.65	4.20	151	34	100	1.30	16	105	Faston 4.8	2					
S306/12 S	NAS3060012VW0SC	6	12.0	11.40	7.20	151	50	100	2.05	10	180	Faston 4.8	2					
S312/1.2 S	NAS31201D2VW0SC	12	1.2	1.10	0.70	97	45	59	0.59	120	18	Faston 4.8	4					
S312/2.3 S	NAS31202D3VW0SC	12	2.3	2.19	1.38	178	34	65	0.94	75	34	Faston 4.8	2					
S312/3 S	NAS3120003VW0SC	12	3.0	2.85	1.80	134	67	66	1.30	60	45	Faston 4.8	2					
S312/4 S	NAS3120004VW0SC	12	4.0	3.80	2.40	90	70	106	1.67	45	60	Faston 4.8	3					
S312/7 S	NAS3120007VW0SC	12	7.0	6.50	4.20	151	65	98	2.60	25	105	Faston 4.8	5					
S312/12 S	NAS3120012VW0SC	12	12.0	11.10	7.20	151	98	98	4.03	18	180	Faston 4.8	5					
S312/18 G5	NAS3120018VW0BC	12	18.0	16.15	10.20	181	76	166	6.15	16	225	Bolt-nut-5	7					
S312/24 G5	NAS3120024VW0BC	12	24.0	22.30	14.40	175	166	125	9.40	10	360	Bolt-nut-5	7					
S312/26 G5	NAS3120026VW0BC	12	26.0	24.70	15.60	175	166	125	9.40	10	360	Bolt-nut-5	7					
S312/40 G5	NAS3120040VW0BC	12	40.0	37.20	24.00	196	165	171	14.30	8	600	Bolt-nut-5	7					


(1): +/-2mm (2): +/-3mm

With VdS approval


Type	Part number	Nominal voltage	Capacity			Length ⁽¹⁾ x Width ⁽¹⁾ x Height ⁽²⁾			Weight approx. kg	Internal resistance mΩ	Max. dis. current A	Terminal	Terminal position					
			C 20	C 10	C 1													
			1,75VpC 20°C	1,75VpC 20°C	1,6VpC 20°C	mm	mm	mm										
V			Ah	Ah	Ah													
S306/10 S	NAS3060010VW0SA	6	10.0	9.3	6.0	151	50.0	97.5	2.00	7	150	Fast-on-4.8	2					
S312/1.2 S	NAS31201D2VW0SA	12	1.2	1.1	0.7	97	47.5	55.0	0.57	120	18	Fast-on-4.8	4					
S312/2 S	NAS3120002VW0SA	12	2.0	1.9	1.2	178	34.0	64.0	0.91	60	30	Fast-on-4.8	2					
S312/3.2 S	NAS31203D2VW0SA	12	3.2	3.0	1.9	134	67.0	63.5	1.40	40	48	Fast-on-4.8	4					
S312/7 S	NAS3120007VW0SA	12	7.0	6.5	4.2	151	65.0	97.5	2.50	30	105	Fast-on-4.8	5					
S312/12 S	NAS3120012VW0SA	12	12.0	11.1	7.2	151	98.0	97.5	4.00	15	180	Fast-on-4.8	5					
S312/18 G5	NAS3120018VW0BA	12	18.0	16.7	10.8	181	76.0	167.0	6.20	11	270	Bolt-nut-5	7					
S312/24 G5	NAS3120024VW0BA	12	24.0	22.3	14.4	175	166.0	125.0	8.70	10	360	Bolt-nut-5	7					
S312/40 G5	NAS3120040VW0BA	12	40.0	37.2	24.0	197	165.0	170.0	14.00	8	600	Bolt-nut-5	7					
S312/65 G6	NAS3120065VW0BA	12	65.0	60.5	39.0	325	166.0	174.0	22.50	5	975	Bolt-nut-6	6					

(1): +/-2mm (2): +/-3mm


Terminal Position




1




2




3




4



5



6



7

Exide Technologies Network Power – The Industry Leader.



Exide Technologies Network Power Division is the global leader in stored electrical energy solutions for all major critical reserve power applications and needs. Network power applications include communication/data networks, UPS systems for computers and control systems, electrical power generation and distribution systems, as well as a wide range of other industrial standby power applications. With a strong manufacturing base in both North America and Europe and a truly global reach (operations in more than 80 countries) in sales and service, Exide Technologies Network Power Division is best positioned to satisfy your back up power needs locally as well as all over the world.

Based on over 100 years of technological innovation the Network Power Division leads the industry with the most recognized global brands such as Absolyte, Sonnnenschein, Marathon, Sprinter, and Flooded Classic. They are bywords for quality, reliability, performance and excellence in all the markets served.

Exide Technologies takes pride in its commitment to a better environment and its Total Battery Management program, an integrated approach to manufacturing, distributing and recycling of lead acid batteries, has been developed to ensure a safe and responsible life cycle for all of its products.

EXIDE Technologies

Network Power
Im Thiergarten
63654 Büdingen
Germany
Tel.: +49 (0) 60 42 / 8170
Fax: +49 (0) 60 42 / 81233

www.exide.com

EXIDE
TECHNOLOGIES