

# UFS3-37P417

UFS

**FORK SENSORS** 





# Ordering information

Туре	Part no.
UFS3-37P417	6075474

Other models and accessories → www.sick.com/UFS

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Ultrasonic detection principle
Dimensions (W x H x D)	20 mm x 37.4 mm x 70 mm
Housing design	Fork shaped
Fork width	2.6 mm
Fork depth	42.5 mm
Minimum detectable object (MDO)	Label size: 2 mm <sup>1)</sup> Label gap: 1 mm <sup>1)</sup>
Label detection	✓
Adjustment	Teach-in button, cable (Teach-in, sensitivity, light/dark switching, Teach-in dynamic)
Teach-in mode	1-point teach-in 2-point teach-in Teach-in dynamic

<sup>&</sup>lt;sup>1)</sup> Depends on the label thickness.

### Mechanics/electronics

Supply voltage	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 10 % <sup>2)</sup>

<sup>1)</sup> Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

 $<sup>^{2)}</sup>$  May not fall below or exceed  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> With light/dark ratio 1:1.

<sup>5)</sup> Signal transit time with resistive load.

<sup>&</sup>lt;sup>6)</sup> Output current minimal 0.03 mA.

 $<sup>^{7)}</sup>$  Reference voltage DC 50 V.

Current consumption50 mA 3)Switching frequency1.1 kHz 4)Response time440 μs 5)Jitter40 μsSwitching outputPNPSwitching output (voltage)PNP: HIGH = V <sub>S</sub> - 3 V / LOW = 0 V
Response time 440 µs <sup>5)</sup> Jitter 40 µs  Switching output PNP
Jitter 40 µs Switching output PNP
Switching output PNP
<b>Switching output (voltage)</b> PNP: HIGH = $V_S - 3 \text{ V} / \text{LOW} = 0 \text{ V}$
Switching mode Light/dark switching
Output current I <sub>max.</sub> 100 mA <sup>6)</sup>
Input, teach-in (ET) Teach: $U < 2 V$ : Run: $U = 10 V < U_V$
Initialization time 100 ms
Connection type Male connector M8, 4-pin
Protection class III 7)
Circuit protection  U <sub>V</sub> connections, reverse polarity protected  Output Q short-circuit protected  Interference pulse suppression
Enclosure rating IP65
Weight Approx. 100 g
Housing material  Zamak Glass fiber reinforced plastic
Indication       LED indicator green: power on         LED indicator, yellow: Status switching output Q

 $<sup>^{1)}</sup>$  Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

#### Communication interface

IO-Link	<b>√</b> , V1.1
Data transmission rate	COM3 (230,4 kBaud)
Cycle time	4 ms
VendorID	26
DeviceID HEX	0x8002A6
DeviceID DEC	8389286
Process data length	16 Bit
Process data structure A	Bit 0 = switching signal $Q_{L1}$ Bit 1 = switching signal $Q_{L2}$ Bit 2 = switching signal $Q_{Int1}$ Bit 3 = switching signal $Q_{Int2}$ Bit 4 = alarm $Q_{OR}$ Bit 5 = Teach busy Bit 6 15 = measured value
Digital output	$Q_1$
Number	1

 $<sup>^{2)}\,\</sup>text{May}$  not fall below or exceed UV tolerances.

<sup>3)</sup> Without load.

<sup>4)</sup> With light/dark ratio 1:1.

<sup>5)</sup> Signal transit time with resistive load.

<sup>6)</sup> Output current minimal 0.03 mA.

<sup>7)</sup> Reference voltage DC 50 V.

#### Ambient data

Ambient operating temperature	+5 °C +55 °C <sup>1)</sup>
Ambient temperature, storage	-20 °C +70 °C
Shock load	According to EN 60068-2-27
EMC	EN 60947-5-2 <sup>2)</sup>
UL File No.	NRKH.E191603 & NRKH7.E191603

 $<sup>^{1)}</sup>$  Do not bend below 0  $^{\circ}\text{C}.$ 

#### Connection type/pinouts

Connection type	Male connector M8, 4-pin
Pinouts	
BN 1	+ (L+)
WH 2	MF
BU 3	- (M)
BK 4	Q/C

#### **Smart Task**

ECLASS 9.0

UNSPSC 16.0901

Smart Task name	Base logics
Classifications	
ECLASS 5.0	27270909
ECLASS 5.1.4	27270909
ECLASS 6.0	27270909

 ECLASS 6.2
 27270909

 ECLASS 7.0
 27270909

 ECLASS 8.0
 27270909

 ECLASS 8.1
 27270909

**ECLASS 10.0** 27270909 **ECLASS 11.0** 27270909

ECLASS 12.0 27270909
ETIM 5.0 EC002720
ETIM 6.0 EC002720


**ETIM 7.0** EC002720 **ETIM 8.0** EC002720


27270909


<sup>&</sup>lt;sup>2)</sup> The sensor complies with the Radio Safety Requirements (EMC) for the industrial sector (Radio Safety Class A). It may cause radio interference if used in a residential area.

# Dimensional drawing (Dimensions in mm (inch))

Dimensional drawing, sensor








- ① Fork depth
- ② Fork width
- 3 Fixing hole
- Detection axis
- ⑤ Connection
- ⑤ Display and adjustment elements

#### **Pinouts**


Pinouts, see table Technical data: Connection type/pinouts



Male connector, M8, 4-pin, uncoded

# Adjustments

Display and adjustment elements



- ① LEDs (status display)
- ② Teach-in button
- ③ Bar graph

#### Recommended accessories

Other models and accessories → www.sick.com/UFS

	Brief description	Туре	Part no.	
Connection modules				
	IO-Link V1.1 Class A port, USB2.0 port, optional external power supply 24V $/$ 1A	IOLA2US-01101 (SiLink2 Master)	1061790	
Universal bar	Universal bar clamp systems			
1	WFS mounting rod, straight, including 2 x fixing screws, Aluminum	BEF-M12GF-A	2059414	
00	Bar clamp for bar diameter of 12 mm (fixing the mounting rod), Aluminum, 2 screws M6 x 30, 2 spring discs	BEF-RMC-D12	5321878	
	<ul> <li>Connection type head A: Female connector, M8, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF8U14- 050VA3XLEAX	2095889	
Sensor Integr	ation Gateway			
Hansley,	Further functions: Web server integrated, IIoT interface available (dual talk)     Logic editor: no     Communication interface: IO-Link, Ethernet, PROFINET, REST API, MQTT, OPC UA     Product category: IO-Link Master	SIG350-0004AP100	6076871	
	Further functions: Web server integrated, IIoT interface available (dual talk)     Logic editor: no     Communication interface: IO-Link, Ethernet, EtherNet/IP™, REST API, MQTT, OPC UA     Product category: IO-Link Master	SIG350-0005AP100	6076923	
	<ul> <li>Further functions: Web server integrated, IIoT interface available (dual talk)</li> <li>Logic editor: no</li> <li>Communication interface: IO-Link, Ethernet, EtherCAT<sup>®</sup>, REST API, MQTT, OPC UA</li> <li>Product category: IO-Link Master</li> </ul>	SIG350-0006AP100	6076924	

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

