


Geberit Mapress Stainless Steel bend (silicone-free)



Example image

APPLICATION PURPOSES

- For cold and hot potable water
 - For cooling and heating water without antifreeze agent
 - For cooling and heating water with antifreeze agent
 - For district heating water ≤ 120 °C
 - For saturated steam ≤ 120 °C
 - For service water and process water
 - For treated water
 - For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
 - For extinguishing water (wet/dry, dry)
 - For sprinklers (wet)
 - For chemicals and technical liquids
 - For compressed air (oil purity class 0–3)
 - For negative pressure
 - For inert gases (e.g. nitrogen)
 - For industrial gases (e.g. acetylene, shielding gases)
 - For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	arc °	L cm	Z cm
80602	12	15	45	2.8	0.8
80603	15	18	45	2.9	0.9
80604	20	22	45	3.2	1.1
80605	25	28	45	3.7	1.4

Art. no.	DN	d _ø mm	arc °	L cm	z cm
82606	32	35	45	4.3	1.7
82607	40	42	45	5.1	2.1
82608	50	54	45	6.2	2.7
82609	65	76.1	45	10.1	4.8
82610	80	88.9	45	11.7	5.7
82611	100	108	45	14.3	6.8
80102	12	15	90	3.8	1.8
80103	15	18	90	4.2	2.2
80104	20	22	90	4.7	2.6
80105	25	28	90	5.7	3.4
81106	32	35	90	6.8	4.2
81107	40	42	90	8	5
81108	50	54	90	10	6.5

Art. no.	DN	d _ø mm	arc °	L cm	Z cm
81109	65	76.1	90	15.7	10.4
81110	80	88.9	90	18.4	12.4
81111	100	108	90	22.6	15.1