

SD-WMTB (70X10) VA - Carrier for conductor marking collar



0826585

<https://www.phoenixcontact.com/gb/products/0826585>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Carrier for conductor marking collar, silver, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 16 mm, text field height: 10 mm, text field width: 70 mm

Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

Commercial data

Item number	0826585
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG231A
Product key	BG231A
Catalog page	Page 246 (C-3-2019)
GTIN	4046356412957
Weight per piece (including packing)	2.03 g
Weight per piece (excluding packing)	2.03 g
Customs tariff number	83100000
Country of origin	SE

SD-WMTB (70X10) VA - Carrier for conductor marking collar



0826585

<https://www.phoenixcontact.com/gb/products/0826585>

Technical data

Product properties

Product type	Marker carrier cable
Type	Marking strip/label

Dimensions

Width	10 mm
Length	70 mm

External dimensions

Outside diameter	10 mm ... 305 mm
------------------	------------------

Text field

Text field width	70 mm
Text field height	10 mm

Material specifications

Color	silver
Material	Stainless steel

Cable/line

External cable diameter	> 16.00 mm
-------------------------	------------

Environmental and real-life conditions

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesa film test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed

SD-WMTB (70X10) VA - Carrier for conductor marking collar



0826585

<https://www.phoenixcontact.com/gb/products/0826585>

Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h

Ambient conditions

Ambient temperature (operation)	-80 °C ... 400 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

SD-WMTB (70X10) VA - Carrier for conductor marking collar



0826585

<https://www.phoenixcontact.com/gb/products/0826585>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SD-WMTB (70X10) VA - Carrier for conductor marking collar



0826585
<https://www.phoenixcontact.com/gb/products/0826585>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk