



Main

Range	TeSys
Range of product	TeSys F
Product or component type	Contactor
Device short name	LC1F
Contactor application	Resistive load
Utilisation category	AC-1
Poles description	3P
[Ue] rated operational voltage	≤ 460 V DC ≤ 690 V AC 50/60 Hz
[Uc] control circuit voltage	230 V DC
[Ie] rated operational current	1260 A (at <40 °C) AC-1

Complementary

[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	1260 A (at 40 °C)
Rated breaking capacity	1890 A conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	3000 A 40 °C - 3 min 8000 A 40 °C - 10 s 5200 A 40 °C - 30 s 4000 A 40 °C - 1 min 2000 A 40 °C - 10 min
Associated fuse rating	1000 A gG at ≤ 440 V
Average impedance	0.12 mOhm - Ith 1260 A 50 Hz
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power dissipation per pole	120 W AC-1
Overvoltage category	III
Power pole contact composition	3 NO
Control circuit voltage limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.2...0.35 Uc (at 55 °C)
Inrush power in W	1600 W (at 20 °C)
Hold-in power consumption in W	9 W at 20 °C
Maximum operating rate	1200 cyc/h 55 °C
Operating time	60...70 ms closing 40...50 ms opening
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² solid without cable end Power circuit: bar 2 cable(s) - busbar cross section: 100 x 5 mm Power circuit: bolted connection
Tightening torque	Control circuit: 1.2 N.m Power circuit: 58 N.m
Mounting support	Plate

Heat dissipation	9 W
Standards	EN 60947-1 IEC 60947-1 JIS C8201-4-1 EN 60947-4-1 IEC 60947-4-1
Product certifications	CB[RETURN]JUL[RETURN]CSA[RETURN]CQC[RETURN]CE[RETURN]UKCA[RETURN]CCC
Compatibility code	LC1F
Control circuit type	DC standard

Environment

Protective treatment	TH
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...60 °C
Height	338 mm
Width	309 mm
Depth	255 mm
Operating altitude	3000 m without derating
Net weight	19 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins