

SCALANCE XR324-4M EEC; Managed IE switch, 19" rack; 16x 10/100/1000 Mbit/s for RJ45 ports electrical; 4x 100/1000 Mbit/s for 2-port media modules, electrical or optical; LED diagnostics; error signaling Contact; Select/set pushbutton, PROFINET IO device, network management, Integrated redundancy manager; Power supply 2x 230 V AC; Ports in the front.



<b>product type designation</b>	<b>SCALANCE XR324-4M EEC</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	24
number of optical ports / maximum	8
<b>interfaces / for communication / integrated</b>	
number of electrical connections	16; RJ45
• for network components or terminal equipment	
number of 100 Mbit/s ST(BFOC) ports	8
• for multimode	
number of 100 Mbit/s SC ports	8
• for multimode	
number of 1000 Mbit/s LC ports	8
• for multimode	8
• for single mode (LD)	8
<b>interfaces / other</b>	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for media module	4
• for power supply	2
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2 x 3-pole terminal block
• for power supply	2 x 3-pole terminal block
design of the removable storage	
• C-PLUG	Yes
<b>signal inputs/outputs</b>	
operating voltage / of the signaling contacts	
• at AC / rated value	276 V
• at DC / rated value	230 V
operational current / of the signaling contacts	
• at AC / maximum	5 A
• at DC / maximum	0.1 A
<b>supply voltage, current consumption, power loss</b>	
type of voltage supply / redundant power supply unit	Yes
<b>type of voltage / 1 / of the supply voltage</b>	AC
• supply voltage / 1 / rated value	230 V
• power loss [W] / 1 / rated value	42 W

<ul style="list-style-type: none"> <li>• supply voltage / 1 / rated value</li> <li>• consumed current / 1 / maximum</li> <li>• type of electrical connection / 1 / for power supply</li> <li>• product component / 1 / fusing at power supply input</li> <li>• fuse protection type / 1 / at input for supply voltage</li> </ul>	80 ... 276 V 0.7 A 2 x 3-pole terminal block Yes 3.15 A / 250 V
<b>type of voltage / 2 / of the supply voltage</b> <ul style="list-style-type: none"> <li>• power loss [W] / 2 / rated value</li> <li>• consumed current / 2 / at rated supply voltage / maximum</li> <li>• supply voltage / 2 / rated value</li> <li>• type of electrical connection / 2 / for power supply</li> <li>• product component / 2 / fusing at power supply input</li> </ul>	DC 42 W 0.7 A 60 ... 250 V 2 x 3-pole terminal block Yes
<b>ambient conditions</b>	
ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> <li>• note</li> </ul>	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C Extended temperature upper limit of +85° C permitted for 16 hours. Reduced operating temperature through the use of media modules (-40 °C to +70 °C) or SFP plug-in transceivers (-40 °C to +60 °C)
relative humidity <ul style="list-style-type: none"> <li>• at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	19" rack
number of modular height units / relating to 19-inch cabinet	1
width	483 mm
height	44 mm
depth	305 mm
net weight	7 kg
fastening method <ul style="list-style-type: none"> <li>• 19-inch installation</li> <li>• 35 mm top hat DIN rail mounting</li> <li>• wall mounting</li> <li>• S7-300 rail mounting</li> <li>• S7-1500 rail mounting</li> </ul>	When used in shipbuilding, the device must be secured in the 19" rack at four points Yes No No No No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <math>\leq 0.3\text{s}</math>	100
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function <ul style="list-style-type: none"> <li>• CLI</li> <li>• web-based management</li> <li>• MIB support</li> <li>• TRAPs via email</li> <li>• configuration with STEP 7</li> <li>• RMON</li> <li>• port mirroring</li> <li>• multipoint mirroring</li> <li>• CoS</li> <li>• PROFINET IO diagnosis</li> </ul>	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
PROFINET conformity class	B
product function / switch-managed	Yes
protocol / is supported <ul style="list-style-type: none"> <li>• Telnet</li> <li>• HTTP</li> <li>• HTTPS</li> <li>• TFTP</li> <li>• FTP</li> <li>• BOOTP</li> </ul>	Yes Yes Yes Yes Yes Yes

• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
<b>product functions / diagnostics</b>	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
<b>product functions / VLAN</b>	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
protocol / is supported / GVRP	Yes
<b>product functions / DHCP</b>	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
<b>product functions / redundancy</b>	
product function	
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes
<b>product functions / security</b>	
product function	
• ACL - MAC-based	Yes
• ACL - port/MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes

<ul style="list-style-type: none"> <li>• broadcast blocking</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• SSH</li> </ul>	Yes
<b>product functions / time</b>	
product function	
<ul style="list-style-type: none"> <li>• SICLOCK support</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• NTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEEE 1588 profile default</li> </ul>	Yes
<b>standards, specifications, approvals</b>	
standard	
<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	UL 508, CSA C22.2 No. 142-M1987
<ul style="list-style-type: none"> <li>• for emitted interference</li> </ul>	EN 61000-6-4:2007 (Class A)
<ul style="list-style-type: none"> <li>• for interference immunity</li> </ul>	EN 61000-6-2:2005
MTBF	20 a
reference code	
<ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> </ul>	KF
<ul style="list-style-type: none"> <li>• according to IEC 81346-2:2019</li> </ul>	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
standard	
<ul style="list-style-type: none"> <li>• for EMC</li> </ul>	IEC 61850, IEEE 1613
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	-
<ul style="list-style-type: none"> <li>• from CSA and UL</li> </ul>	No
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> <li>• C-Tick</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• KC approval</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEC 61850-3</li> </ul>	Yes
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
<ul style="list-style-type: none"> <li>• French marine classification society (BV)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Korean Register of Shipping (KRS)</li> </ul>	Yes
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
<ul style="list-style-type: none"> <li>• to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>• to website: Industry Mall</li> </ul>	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
<ul style="list-style-type: none"> <li>• to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
<ul style="list-style-type: none"> <li>• to website: Selection guide for cables and connectors</li> </ul>	<a href="https://sie.ag/2QdlxcP">https://sie.ag/2QdlxcP</a>
<ul style="list-style-type: none"> <li>• to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>• to website: CAx-Download-Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>• to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial security measures that may be implemented, please visit <a href="https://www.siemens.com/industrialsecurity">https://www.siemens.com/industrialsecurity</a>. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under <a href="https://www.siemens.com/cert">https://www.siemens.com/cert</a>. (V4.6)</p>

Approvals / Certificates

General Product Approval	EMC	Declaration of Conformity			
--------------------------	-----	---------------------------	--	--	--



[Manufacturer Declaration](#)



Test Certificates Marine / Shipping

[Type Test Certificates/Test Report](#)



[NK / Nippon Kaiji Kyokai](#)



Marine / Shipping



last modified:

11/9/2023